

Diode block - EMG 22-DIO 4M-1N5408 - 2952211

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Diode module, with four diodes, common anode, diode type 1N 5408

Your advantages

- Spark-suppression diodes for limiting surge voltages of inductive loads
- Electrical decoupling of messages in fault reporting systems



Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 084370
GTIN	4017918084370
Weight per Piece (excluding packing)	46.270 g
Custom tariff number	85411000
Country of origin	Germany

Technical data

Dimensions

Width	22.5 mm
Height	75 mm
Depth	55 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Diode type	1 N 5408
Peak reverse voltage per diode	1000 V
Reverse current per diode	10 µA

Diode block - EMG 22-DIO 4M-1N5408 - 2952211

Technical data

General

Conducting state voltage per diode	approx. 0.8 V
Conducting state current per diode	1.5 A (with single load)
	1 A (with simultaneous loads)
Mounting position	any
Assembly instructions	In rows with zero spacing

Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Standards and Regulations

Standards/regulations	DIN EN 50178
Pollution degree	2

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27250300
eCl@ss 4.1	27260800
eCl@ss 5.0	27371000
eCl@ss 5.1	27371000
eCl@ss 6.0	27371000
eCl@ss 7.0	27371010
eCl@ss 8.0	27371010
eCl@ss 9.0	27371010

ETIM

ETIM 4.0	EC000683
ETIM 5.0	EC000683
ETIM 6.0	EC000683
ETIM 7.0	EC000683

Diode block - EMG 22-DIO 4M-1N5408 - 2952211

Classifications

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	32151504
UNSPSC 18.0	32151504
UNSPSC 19.0	32151504
UNSPSC 20.0	32151504
UNSPSC 21.0	32151504

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU*DE*08.B.01841/19
-----	--	---------------------

Accessories

Accessories

Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material
