

## Electronic housing - EMG 37-B7 - 2947064

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Custom circuit module, consisting of housing, MKDS 3 connection terminal blocks and PCB

### Your advantages

- ✓ Choice of four cover sizes in transparent or color versions
- ✓ Practical and easy-to-wire conductor connections
- ✓ Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- ✓ Uniform and appropriate housing technology
- ✓ High degree of flexibility due to the wide choice of versions
- ✓ User-friendly and safe mounting on DIN rails according to EN 60715
- ✓ Inflammability class V0 insulation material (according to UL 94)
- ✓ Shock and contamination-proof accommodation of electronic components
- ✓ Universal PCBs for all pitches

### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 082536
GTIN	4017918082536
Weight per Piece (excluding packing)	74.450 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### General

Housing type	Component housing
Housing material	Polycarbonate fiber reinforced
Color (RAL)	green

# Electronic housing - EMG 37-B7 - 2947064

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Dimensions

Length	75 mm
Height	47.5 mm
Width	37.5 mm
Pitch	5 mm
Depth	75 mm

### Technical data

Power dissipation without gap	1.6 W
Power dissipation with 20 mm gap	1.8 W
Number of positions	14

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing




1 = Top edge of the PCB

# Electronic housing - EMG 37-B7 - 2947064

B = Housing width

Dimensional drawing



Pitch 5 mm

a = Area for mounting components, 38 mm in the hood

b = Area for mounting components, 45 mm in the housing

## Classifications

eCl@ss

eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

# Electronic housing - EMG 37-B7 - 2947064

## Classifications

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		B.01742
-----	--	---------

## Accessories

### Accessories

### Device marking

Marking material - EMG-GKS 22 - 2941594



Device marking label, width: 22 mm, area: 22 x 8 mm, e.g. for EML(20x8) R adhesive marking material

### Filler plug

---

## Electronic housing - EMG 37-B7 - 2947064

### Accessories

Electronic housing - EMG-KA - 2941510



Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.

---

Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

---

Marking material - EMG-SGKS 10 - 2947585



Equipment marker, narrow

---

### Necessary add-on products

Covering hood - EMG 37-H 7,5MM KLAR - 2947158



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm

---

Covering hood - EMG 37-H 15MM KLAR - 2947161



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 37.5 mm

---

## Electronic housing - EMG 37-B7 - 2947064

### Accessories

Covering hood - EMG 37-H 35MM KLAR - 2942768



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 35 mm, width: 37.5 mm

---

Electronic housing - EMG 37-H 52MM GN - 2947174



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 37.5 mm

---

---