

Printed-circuit board connector - GMSTBT 2,5 HV/3-ST-7,25 BK - 2202104


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PCB connector, number of positions: 3



Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 990141
GTIN	4046356990141
Weight per Piece (excluding packing)	6.230 g
Custom tariff number	85366990
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

General

Number of positions	3
Insulating material group	I

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Printed-circuit board connector - GMSTBT 2,5 HV/3-ST-7,25 BK - 2202104

Classifications

eCl@ss

eCl@ss 10.0.1	27440290
eCl@ss 5.1	27261100
eCl@ss 6.0	27261100
eCl@ss 7.0	27440401
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 4.0	EC002643
ETIM 5.0	EC002638
ETIM 6.0	EC002638
ETIM 7.0	EC002638

UNSPSC

UNSPSC 13.2	39121432
UNSPSC 18.0	39121409
UNSPSC 19.0	39121409
UNSPSC 20.0	39121409
UNSPSC 21.0	39121409

Approvals

Approvals

Approvals

EAC / cULus Recognized / CCA / IECCEB Scheme / VDE Gutachten mit Fertigungsüberwachung


Ex Approvals

Approval details


EAC		B.01742
-----	---	---------


Printed-circuit board connector - GMSTBT 2,5 HV/3-ST-7,25 BK - 2202104

Approvals

cULus Recognized  http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E60425-19931013		
	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	16 A	16 A
mm ² /AWG/kcmil	24-12	24-12

CCA		CCA/DE1 34305/A1
Nominal voltage UN	630 V	
Nominal current IN	16 A	

IECEE CB Scheme  http://www.iecee.org/ DE1-52506/A1	
Nominal voltage UN	630 V
Nominal current IN	16 A

VDE Gutachten mit Fertigungsüberwachung  http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx 40037875	
Nominal voltage UN	630 V
Nominal current IN	16 A
mm ² /AWG/kcmil	0.2-2.5