

Media module - FL SFP LX - 2891767

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Gigabit SFP module for transmission up to 30 km with a wavelength of 1310 nm.


The figure shows a version of the product

Product Description

SFP module with a data transmission speed of 1000 Mbps, a wavelength of 1310 nm, and a maximum transmission length of 30 km.



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 166775
GTIN	4046356166775
Weight per Piece (excluding packing)	28.600 g
Custom tariff number	85176200
Country of origin	Taiwan

Technical data

Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

Media module - FL SFP LX - 2891767

Technical data

Interfaces

Interface	Ethernet FO
No. of ports	1 (LC single mode)
Transmission physics	Single-mode fiberglass
Transmission speed	1 Gbps
Transmission length	30 km (Fiberglass 9/125)
	250 m (Fiberglass 62.5/125)
Wavelength	1310 nm
Signal LEDs	depending on the Factoryline device

Function

Basic functions	SFP module as FO port
Status and diagnostic indicators	via a Factoryline device

Supply voltage

Supply voltage	3.3 V (via Factoryline switch)
Max. current consumption	300 mA
Current consumption	300 mA

General

Mounting type	Insert in SFP slot
Type AX	Factoryline devices with SFP slot
Net weight	28.6 g
Housing material	Metal

Standards and Regulations

Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Connection in acc. with standard	CUL
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

Classifications

eCl@ss

eCl@ss 10.0.1	19179290
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	27250500
eCl@ss 5.1	27250500
eCl@ss 6.0	27250500
eCl@ss 7.0	27250501
eCl@ss 8.0	27149249
eCl@ss 9.0	19179290

Media module - FL SFP LX - 2891767

Classifications

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC002609
ETIM 6.0	EC000310
ETIM 7.0	EC000310

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	26121650
UNSPSC 18.0	43222604
UNSPSC 19.0	43222604
UNSPSC 20.0	43222604
UNSPSC 21.0	43222604

Approvals

Approvals


Approvals

DNV GL / LR / BSH / RINA / UL Recognized / cUL Recognized / ABS / NK / BV / EAC / cULus Recognized

Ex Approvals

Approval details

DNV GL		https://approvalfinder.dnvgl.com/	TAA00000YV
--------	---	---	------------

LR		http://www.lr.org/en	17/20056
----	---	---	----------

BSH		http://www.bsh.de/de/index.jsp	Nr. 966
-----	--	---	---------

Media module - FL SFP LX - 2891767

Approvals

RINA		http://www.rina.org/en	ELE130419XG
UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
ABS		http://www.eagle.org/eagleExternalPortalWEB/	17- HG1592765-1-PDA
NK		http://www.classnk.or.jp/hp/en/	TA19464M
BV		http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials	48146/A0 BV
EAC			RU*DE*08.B.00731/19
cULus Recognized			

Accessories

Accessories

Data cable preassembled

FO patch cable - FL SM PATCH 1,0 LC-LC - 2989187



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 µm (OS2, Low Water Peak Fiber), connector: LC/LC, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 1 m

Media module - FL SFP LX - 2891767

Accessories

FO patch cable - FL SM PATCH 2,0 LC-LC - 2989284



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber), connector: LC/LC, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 2 m

FO patch cable - FL SM PATCH 5,0 LC-LC - 2901826



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber), connector: LC/LC, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 5 m

FO patch cable - FL SM PATCH 1,0 LC-SC - 2989190



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber) connector: LC/SC duplex, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 1 m

FO patch cable - FL SM PATCH 2,0 LC-SC - 2989297



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber) connector: LC/SC duplex, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 2 m

FO patch cable - FL SM PATCH 5,0 LC-SC - 2901827



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber) connector: LC/SC duplex, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 5 m

Media module - FL SFP LX - 2891767

Accessories

FO patch cable - FL SM PATCH 1,0 LC-ST - 2989242



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber), connector: LC/B-FOC(ST®), degree of protection: IP20, for installation in cable ducts or control cabinets, length: 1 m

FO patch cable - FL SM PATCH 2,0 LC-ST - 2989349



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber), connector: LC/B-FOC(ST®), degree of protection: IP20, for installation in cable ducts or control cabinets, length: 2 m

FO patch cable - FL SM PATCH 5,0 LC-ST - 2901828



Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 μm (OS2, Low Water Peak Fiber), connector: LC/B-FOC(ST®), degree of protection: IP20, for installation in cable ducts or control cabinets, length: 5 m
