

## Miniature solid-state relay - SIM-EI- 24DC/TTL/100 - 2271154

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Input solid-state relay, with protective circuit in input and output circuits, input: 24 V DC, output: TTL logic level, max. 100 mA

The figure shows version SIM-EI-5DC/TTL/100



### Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 054199
GTIN	4017918054199
Weight per Piece (excluding packing)	19.670 g
Custom tariff number	85364190
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	13 mm
Height	29 mm
Depth	25 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### Input data

Nominal input voltage $U_N$	24 V AC
Input voltage range in reference to $U_N$	0.9 ... 1.1
Input voltage range	21.6 V DC ... 26.4 V DC
Switching threshold "0" signal in reference to $U_N$	$\leq 0.4$

## Miniature solid-state relay - SIM-EI- 24DC/TTL/100 - 2271154

### Technical data

#### Input data

Switching threshold "1" signal in reference to $U_N$	$\geq 0.8$
Typical input current at $U_N$	5.1 mA
Type of protection	Reverse polarity protection
Protective circuit/component	Polarity protection diode
Transmission frequency	4000 Hz

#### Output data

Output voltage range	3 V DC ... 5.25 V DC
Limiting continuous current	100 mA
Fan out	1
Voltage drop at max. limiting continuous current	0.3 V
Output circuit	3-conductor, ground-referenced
Type of protection	Reverse polarity protection
	Free running
Protective circuit/component	Polarity protection diode
	Damping diode
Output resistor	approx. 390 $\Omega$

#### General

Test voltage input/output	2.5 kV (50 Hz, 1 min.)
Mounting position	any
Assembly instructions	Can be aligned with 2 mm spacing

#### Standards and Regulations

Standards/regulations	DIN VDE 0110
-----------------------	--------------


#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings

# Miniature solid-state relay - SIM-EI- 24DC/TTL/100 - 2271154

Dimensional drawing



## Classifications

eCl@ss

eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27371000
eCl@ss 5.1	27371000
eCl@ss 6.0	27371600
eCl@ss 7.0	27371604
eCl@ss 8.0	27371604
eCl@ss 9.0	27371604

ETIM

ETIM 2.0	EC001504
ETIM 3.0	EC001504
ETIM 4.0	EC001504
ETIM 5.0	EC001504
ETIM 6.0	EC001504
ETIM 7.0	EC001504

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121542

# Miniature solid-state relay - SIM-EI- 24DC/TTL/100 - 2271154

## Classifications

### UNSPSC

UNSPSC 11	39121542
UNSPSC 12.01	39121542
UNSPSC 13.2	39122326
UNSPSC 19.0	39122326

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		TR_TS_D_00573_c
-----	-------------------------------------------------------------------------------------	-----------------

---