

Acoustic element - PSD-S AE V15/1 - 2700140

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Voice output element, 24 V DC, max. 50 mp3 or wav files can be saved, max. 15 files can be controlled, black

Your advantages

- ✔ Multilingual signaling thanks to voice output
- ✔ Up to 50 mp3 or wav files can be saved
- ✔ The volume can be set via potentiometer
- ✔ The volume can be set via configuration software
- ✔ The volume can be reduced using up to two control cables
- ✔ Maximum volume of 88 dB(A)

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 491327
GTIN	4046356491327
Weight per Piece (excluding packing)	267.500 g
Custom tariff number	85318070
Country of origin	Germany

Technical data

Dimensions

Diameter	71.5 mm
Height	110 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Degree of protection	IP65, when installed

General

Material	Polycarbonate PC
----------	------------------

Acoustic element - PSD-S AE V15/1 - 2700140

Technical data

General

Color	black
Weight	184 g
Mounting position	any
Scope of delivery	USB cable, software for configuring the voice output element, and user manual on the element

Electrical data

Input voltage	24 V DC \pm 10 %
Nominal input voltage range	21.6 V DC ... 26.4 V DC
Maximum inrush current	max. 3 A (for approximately 2 ms)
Current consumption	< 50 mA (in standby mode)
Service life, electrical	min. 5,000 h
Operating time	100 %
Type of acoustic signal	Voice, max. 15 texts
Volume	approx. 88

Approvals / conformities

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Acoustic element - PSD-S AE V15/1 - 2700140

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27240200
eCl@ss 4.1	27240200
eCl@ss 5.0	27371200
eCl@ss 5.1	27371200
eCl@ss 6.0	27371200
eCl@ss 7.0	27371214
eCl@ss 8.0	27371214
eCl@ss 9.0	27371214

Acoustic element - PSD-S AE V15/1 - 2700140

Classifications

ETIM

ETIM 3.0	EC001026
ETIM 4.0	EC001026
ETIM 5.0	EC001261
ETIM 6.0	EC001026
ETIM 7.0	EC001026

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121311

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / EAC / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 123528
------------	--	---	---------------

EAC		EAC-Zulassung
-----	--	---------------

EAC		RU *- DE.A*30.B.00237
-----	--	--------------------------

Acoustic element - PSD-S AE V15/1 - 2700140

Approvals

cULus Listed



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>