

## DIN rail perforated - NS 15 PERF 1000MM - 1207646


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, Standard profile, width: 15 mm, height: 5.5 mm, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 1000 mm, color: silver

RoHS

### Key Commercial Data

Packing unit	20 pc
Minimum order quantity	20 pc
GTIN	 4 046356 366045
GTIN	4046356366045
Weight per Piece (excluding packing)	999.000 g
Custom tariff number	72166190
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	5.5 mm
Length	1000 mm
Width	15 mm
Hole width	12.20 mm
Hole height	4.20 mm
Drill hole spacing	20.00 mm

#### General

Material	Steel
Coating	galvanized, passivated with a thick layer
Color	silver

#### Standards and Regulations

Test standard	acc. to EN 60715
---------------	------------------

# DIN rail perforated - NS 15 PERF 1000MM - 1207646

## Technical data

### Standards and Regulations


Connection in acc. with standard	IEC / EN
----------------------------------	----------

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Dimensional drawing



## Classifications

eCl@ss

eCl@ss 4.0	23150300
------------	----------

## DIN rail perforated - NS 15 PERF 1000MM - 1207646

### Classifications

#### eCl@ss

eCl@ss 4.1	23150300
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27400600
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

#### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212
ETIM 6.0	EC001285
ETIM 7.0	EC001285

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708
UNSPSC 18.0	39121708
UNSPSC 19.0	39121708
UNSPSC 20.0	39121708
UNSPSC 21.0	39121708