

Europe connectors - EC 6 3POL - 3240676

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Europe terminal strip consisting of polypropylene, white, to connect solid and stranded conductors with and without ferrules with a cross section from 0.75 to 6 mm², 3-pos.

Your advantages

- ✓ The polypropylene insulating housing enables individual positions to be disconnected simply by twisting and without the need for tools
- ✓ The high-quality metal parts, which feature corrosion-resistant surfaces, are fixed securely in the housing
- ✓ The prismatic clamping part facilitates conductor entry and reliable contact can be established even for conductors without ferrules

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 639422
GTIN	4046356639422
Weight per Piece (excluding packing)	6.300 g
Custom tariff number	85369010
Country of origin	Austria

Technical data

General

Number of positions	3
Number of levels	1
Number of connections	6
Nominal cross section	6 mm ²
Color	white
Insulating material	PP
Flammability rating according to UL 94	-
Ambient temperature (operation)	-40 °C ... 80 °C
Maximum load current	41 A (with 6 mm ² conductor cross section)
Nominal current I _N	41 A (with 6 mm ² conductor cross section)

Europe connectors - EC 6 3POL - 3240676

Technical data

General

Nominal voltage U_N	450 V (Only use up to 250 V without securing.)
Open side panel	No

Dimensions

Width	18.9 mm
Length	29.2 mm
Height	14.9 mm
Depth	18.9 mm
Drill hole spacing	10 mm
Pitch	10 mm

Connection data

Connection method	Screw connection
Screw thread	M3
Stripping length	6 mm
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm
Conductor cross section solid min.	0.75 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section AWG min.	18
Conductor cross section AWG max.	10
Conductor cross section flexible min.	0.75 mm ²
Conductor cross section flexible max.	6 mm ²
Min. AWG conductor cross section, flexible	18
Max. AWG conductor cross section, flexible	10
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.75 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.75 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, solid min.	0.75 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.75 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, minimum	0.5 mm ²
Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, maximum	1 mm ²
Two conductors with the same cross section stranded, with ferrule and without plastic sleeve, minimum	0.5 mm ²
Two conductors with the same cross section stranded, with ferrule and without plastic sleeve, maximum	1 mm ²

Standards and Regulations

Flammability rating according to UL 94	-
--	---

Europe connectors - EC 6 3POL - 3240676

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141106
eCl@ss 8.0	27141106
eCl@ss 9.0	27141106

ETIM

ETIM 4.0	EC001284
ETIM 5.0	EC001284
ETIM 6.0	EC001284
ETIM 7.0	EC001284

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121409
UNSPSC 18.0	39121409
UNSPSC 19.0	39121409
UNSPSC 20.0	39121409
UNSPSC 21.0	39121409

Approvals

Approvals

Approvals


EAC

Ex Approvals

Europe connectors - EC 6 3POL - 3240676

Approvals

Approval details

EAC		RU C- DE.BL08.B.00534
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>