




Harnessing > Heat Shrink Components > Breakouts/Transitions



Molded Part Shape: **Y Shape**

Number of Branches/Legs: **5**

Material Code: **25**

Material Systems Code: **25**

Adhesive Pre-Coat: **Yes**

Features

Product Type Features

Molded Part Shape	Y Shape
Size Code	011

Configuration Features

Number of Branches/Legs	5
-------------------------	---

Body Features

Material	Fluid Resistant Modified Elastomer
Material Code	25
Material Systems Code	25
Adhesive Pre-Coat	Yes

Dimensions

Inside Diameter Range (Leg 2)	3.5 – 6.6 mm [.14 – .26 in]
Inside Diameter Range (Leg 3)	3.5 – 6.6 mm [.14 – .26 in]
Inside Diameter Range (Body)	6.9 – 13.2 mm [.27 – .52 in]
Inside Diameter Range (Leg 1)	3.5 – 6.6 mm [.14 – .26 in]
Inside Diameter Range (Leg 4)	3.5 – 6.6 mm [.14 – .26 in]

Usage Conditions

Operating Temperature Range	-75 – 150 °C [-103 – 302 °F]
-----------------------------	------------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----

Industry Standards

Government Qualified	No
----------------------	----

Other

Adhesive Code	86
Molded Part Shape Code	562A
Fluid/Chemical Resistance	Long-Term Exposure at High Temperature
Adhesive Options	/86 Precoat
Adhesive Type	High Performance Pre-Coat Adhesive

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Model / Part # CJ2087-000
HL2010E-KIT-120V


Customers Also Bought



TE Model / Part #924869-000
462A011-25/86-0




TE Model / Part #879364-000
382A012-25/86-0




TE Model / Part #809138-000
202D121-3-60/42-0




TE Model / Part #2101551-1
PLUG,40 POS,Sz105,w/SOLDER CUPS,
140 POT




TE Model / Part #246221-000
KTKK-2617




TE Model / Part #533821-000
TXR21AB00-0804AI



TE Model / Part #840851-000
462A421-71/86-0



TE Model / Part #879492-000
202C621-51/86-0



TE Model / Part #806245-000
202C642-51/86-0



TE Model / Part #533523-000
LNCL-14-185-GK

Documents

Product Drawings

[562A011-25/86-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-25](#)



English

Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English