

PRODUCT-DETAILS

HK1-02

HK1-02 Auxiliary Contact



General Information

Extended Product Type	HK1-02
Product ID	1SAM201902R1003
EAN	4013614320385
Catalog Description	HK1-02 Auxiliary Contact
Long Description	HK1-02 Aux.-contact 2 NC

Ordering

Minimum Order Quantity	2 piece
Customs Tariff Number	85365080

Popular Downloads

Data Sheet, Technical Information	1SBC100192C02--
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802

Dimensions

Product Net Width	9 mm
Product Net Height	90 mm

Product Net Depth / Length	78.5 mm
Product Net Weight	0.035 kg

Technical

Terminal Type	Screw Terminals
Rated Operational Voltage	690 V AC 600 V DC Main Circuit 690 V
Rated Operational Current AC-15 (I _e)	(240 V) 4 A (24 V) 6 A (380 / 400 V) 3 A (690 V) 1 A
Rated Operational Current DC-13 (I _e)	(125 V) 0.55 A (24 V) 2 A (250 V) 0.27 A (440 V) 0.15 A (600 V) 0.15 A
Rated Impulse Withstand Voltage (U _{imp})	Auxiliary Circuit 6 kV
Rated Insulation Voltage (U _i)	690 V
Degree of Protection	IP20
Electrical Durability	100000 cycle
Mechanical Durability	100000 cycle
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible 1/2x 0.75 ... 1.5 mm ² Rigid 1/2x 1 ... 1.5 mm ²
Tightening Torque	Auxiliary Circuit 0.8 ... 1.2 N·m
Wire Stripping Length	Auxiliary Circuit 8 mm
Recommended Screw Driver	M3 Pozidriv 2
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts CO (SPDT)	0
Standards	CSA 22.2 No. 14 IEC/EN 60947-1 IEC/EN 60947-5-1 UL 508 UL 60947-1 UL 60947-5-1
Product Name	Auxiliary Contact
Suitable For	MS116 MS132 MO132 MS165 MO165
Suitable for Product Class	Manual Motor Starter
Accessory Group	Electrical
Accessory Type	Auxiliary Contact

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Connecting Capacity Auxiliary Circuit UL/CSA	Flexible 1/2x 16-14 AWG Stranded 1/2x 16-14 AWG

Tightening Torque UL/CSA	Auxiliary Circuit 7 in-lb
Contact Rating UL/CSA	B600 Q600

Environmental

Ambient Air Temperature	Operation -25 ... +60 °C Storage -50 ... +80 °C
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 25g
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ABS Certificate	1SAA963001-0101
BV Certificate	1SAA963002-0201
CB Certificate	1SAA963001-2002
CCC Certificate	1SAA963003-3802
cUL Certificate	cUL_E137861
Declaration of Conformity - CE	1SAD938503-0304 1SAD938504-0196 1SAD938507-0190 1SAD938504-0198 1SAD938505-0197 1SAD938506-0191 1SAD938507-0188 1SAD938508-0183 1SAD938514-0125 1SAD938521-0060
DNV GL Certificate	1SAA963001-0304
GOST Certificate	1SAA937000-2703
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802
LR Certificate	1SAA963001-0502 1SAA963001-0501 1SAA963000-0505 1SAA918001-0501
RINA Certificate	Rina_MS132
RoHS Information	1SAA963001-4407
UL Certificate	UL_E137861

Container Information

Package Level 1 Width	25 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Height	93 mm
Package Level 1 Gross Weight	0.08 kg
Package Level 1 EAN	4013614481475
Package Level 1 Units	box 2 piece
Package Level 2 Width	280 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Height	210 mm
Package Level 2 Gross Weight	6.775 kg
Package Level 2 EAN	4013614522796
Package Level 2 Units	carton 160 piece

Classifications

Object Classification Code		Q
ETIM 4	EC002498 - Accessories for low-voltage switch technology	
ETIM 5	EC000041 - Auxiliary contact block	
ETIM 6	EC000041 - Auxiliary contact block	
ETIM 7	EC000041 - Auxiliary contact block	
eClass		7.0 27371302
UNSPSC		39121522
IDEA Granular Category Code (IGCC)	4742 >> Electrical contacts	
E-Number (Sweden)		3112009

Categories

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters Accessories

