

Carrier for conductor marking collar - SD-WMTB (92X10) VA - 0826598

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Carrier for conductor marking collar, silver, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 16 mm, lettering field size: 92 x 10 mm

Your advantages

- ✓ Easy assembly with UNIFOX-CT M7,9
- ✓ Secured using stainless steel cable binders
- ✓ The individual stainless steel markers are pushed onto the corresponding holders
- ✓ Cable markers for marking cables and conductors with larger cross sections

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 046356 412964 |
| GTIN | 4046356412964 |
| Weight per Piece (excluding packing) | 2.600 g |
| Custom tariff number | 83100000 |
| Country of origin | Sweden |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 92 mm |
| Width (a) | 10 mm |

General

| | |
|-----------------|-----------------------------|
| Color | silver |
| Type | Marking strip/label |
| Material | Stainless steel |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |

Carrier for conductor marking collar - SD-WMTB (92X10) VA - 0826598

Technical data

General

| | |
|-----------------------|-----------------------------|
| Marking mounting type | Assembly with cable binders |
|-----------------------|-----------------------------|

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |
|------------|---|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27149100 |
| eCl@ss 5.1 | 27400400 |
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149129 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |