

Shrink sleeve - WMS 38,1 (EX60)R - 0800298

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK W: without print, unperforated, mounting type: slide-on, cable diameter range: 12.7 ... 38.1 mm, lettering field size: 60 x 15000 mm

Your advantages

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- UL 224 (125°C, 600 V, all tubing)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- Individual markers can be cut to any length up to 1 m

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 625876 |
| GTIN | 4046356625876 |
| Weight per Piece (excluding packing) | 838.000 g |
| Custom tariff number | 39173200 |
| Country of origin | China |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|----------------|---------------------|
| Length (b) | 15 m |
| Width (a) | 60 mm |
| Cable diameter | 12.7 mm ... 38.1 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -55 °C ... 135 °C |
|---------------------------------|-------------------|

Shrink sleeve - WMS 38,1 (EX60)R - 0800298

Technical data

Ambient conditions

| | |
|--------------------------------|---|
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
|--------------------------------|---|

General

| | |
|---|-------------------------------------|
| Color | white |
| Base element material | polyolefine |
| Type | Shrink sleeve |
| Components | halogen-free |
| Material | Polyolefine |
| RoHS compliant | Yes |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Printing | without print |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Result of weather resistance test | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test | Test passed |
| Marking mounting type | slide-on |

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |
|------------|---|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190200 |
| eCl@ss 4.1 | 24190200 |
| eCl@ss 5.0 | 27400100 |
| eCl@ss 5.1 | 27400100 |
| eCl@ss 6.0 | 27400100 |
| eCl@ss 7.0 | 27400105 |
| eCl@ss 8.0 | 27400105 |
| eCl@ss 9.0 | 27400401 |

Shrink sleeve - WMS 38,1 (EX60)R - 0800298

Classifications

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC001530 |
| ETIM 4.0 | EC000217 |
| ETIM 5.0 | EC000217 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |

Approvals

Approvals

Approvals

CSA / UL Recognized

Ex Approvals

Approval details

| | | | |
|-----|--|---|--------|
| CSA | | http://www.csagroup.org/services-industries/product-listing/ | 252259 |
|-----|--|---|--------|

| | | | |
|---------------|--|---|---------------|
| UL Recognized | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 310982 |
|---------------|--|---|---------------|

Accessories

Accessories

Ink ribbon

Shrink sleeve - WMS 38,1 (EX60)R - 0800298

Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm
