

PRODUCT-DETAILS

# AF26Z-30-00-21

## AF26Z-30-00-21 24-60V50/60HZ 20-60VDC

### Contactors



#### General Information

Extended Product Type	AF26Z-30-00-21
Product ID	1SBL236001R2100
EAN	3471523114111
Catalog Description	AF26Z-30-00-21 24-60V50/60HZ 20-60VDC Contactor

Long Description	<p>AF26Z contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF..Z contactors include an electronic coil interface accepting a wide control voltage <math>U_c \text{ min.} \dots U_c \text{ max.}</math> Only four coils cover control voltages between 24...250 V 50/60 Hz or 12...250 V DC. AF..Z contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF..Z contactors allow direct control by PLC-output <math>\geq 24 \text{ V DC } 500 \text{ mA}</math> and obtain a reduced holding coil consumption. AF..Z contactors withstand short voltage dips and voltage sags (SEMI F47-0706 compliance) between 24...250 V 50/60 Hz AF..Z contactors have built-in surge protection and do not require additional surge suppressors The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, front and side-mounted add-on auxiliary contact blocks. (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available.</p>
------------------	---

#### Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching

ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529
E-Number (Sweden)	3211376

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	87 mm
Package Level 1 Depth / Length	87 mm
Package Level 1 Height	47 mm
Package Level 1 Gross Weight	0.35 kg
Package Level 1 EAN	3471523114111
Package Level 2 Units	box 21 piece
Package Level 2 Width	250 mm
Package Level 2 Depth / Length	300 mm
Package Level 2 Height	315 mm
Package Level 2 Gross Weight	15.75 kg
Package Level 3 Units	1080 piece

## Certificates and Declarations (Document Number)

ABS Certificate	ABS_15-GE1349500-PDA_90682247
BV Certificate	BV_2634H24898B0
CB Certificate	CB_SE-80872M3
CCC Certificate	CCC_2010010304445623
cUL Certificate	UL_20180227_E312527_7_1
Declaration of Conformity - CE	1SBD250000U1000
DNV Certificate	DNV-GL_TAE00001AF-3
DNV GL Certificate	DNV-GL_TAE00001AF-3
EAC Certificate	EAC_RU C-FR ME77 B03597
Environmental Information	1SBD250149E1000
GL Certificate	DNV-GL_TAE00001AF-3
GOST Certificate	GOST_POCCFR.ME77.B07175.pdf
Instructions and Manuals	1SBC101027M6801
KC Certificate	KC_HW02016-15001A
LR Certificate	LRS_1300087E1
RINA Certificate	RINA_ELE240318XG
RMRS Certificate	RMRS_1802705280
RoHS Information	1SBD250000U1000
UL Certificate	UL_20140305-E312527_7_1
UL Listing Card	E312527

---

**Technical UL/CSA**


---

General Use Rating UL/CSA	(600 V AC) 45 A
Horsepower Rating UL/CSA	(220 ... 240 V AC) Three Phase 7-1/2 hp (440 ... 480 V AC) Three Phase 15 hp (550 ... 600 V AC) Three Phase 20 hp (120 V AC) Single Phase 2 hp (200 ... 208 V AC) Three Phase 7-1/2 hp (240 V AC) Single Phase 3 hp
Tightening Torque UL/CSA	Control Circuit 11 IA Main Circuit 22 IA

---



---

**Environmental**


---

Ambient Air Temperature	Close to Contactor for Storage -60 ... +80 °C Close to Contactor without Thermal O/L Relay -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +60 °C
Climatic Withstand	Category B according to IEC 60947-1 Annex Q
Maximum Operating Altitude Permissible	3000 m
Resistance to Vibrations acc. to IEC 60068-2-6	5 ... 300 Hz 4 g closed position / 2 g open position
Resistance to Shock acc. to IEC 60068-2-27	Shock Direction: A 30 K40 Shock Direction: B2 15 K40 Shock Direction: C1 25 K40 Shock Direction: C2 25 K40 Closed, Shock Direction: B1 25 K40 Open, Shock Direction: B1 5 K40
RoHS Status	Following EU Directive 2011/65/EU

---



---

**Technical**


---

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	0
Standards	IEC 60947-1 / 60947-4-1 and EN 60947-1 / 60947-4-1, UL 508, CSA C22.2 N° 14
Rated Operational Voltage	Main Circuit 690 V
Rated Frequency (f)	Main Circuit 50 / 60 Hz
Conventional Free-air Thermal Current ( $I_{th}$ )	acc. to IEC 60947-4-1, Open Contactors $q = 40$ °C 50 A
Rated Operational Current AC-1 ( $I_e$ )	(690 V) 40 °C 45 A (690 V) 60 °C 40 A (690 V) 70 °C 32 A
Rated Operational Current AC-3 ( $I_e$ )	(220 / 230 / 240 V) 60 °C 26 A (380 / 400 V) 60 °C 26 A (415 V) 60 °C 26 A (440 V) 60 °C 26 A (500 V) 60 °C 23 A (690 V) 60 °C 17 A
Rated Operational Power	(220 / 230 / 240 V) 6.5 KWT (380 / 400 V) 11 KWT

AC-3 ( $P_e$ )	(415 V) 11 KWT (440 V) 15 KWT (500 V) 15 KWT (690 V) 15 KWT (400 V) 11 KWT
Rated Short-time Withstand Current ( $I_{cw}$ )	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 350 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 50 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 700 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 225 A for 1 s -empty- A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 440 V 500 A cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 690 V 200 A
Maximum Electrical Switching Frequency	AC-1 600 cycles per hour AC-2 / AC-4 150 cycles per hour AC-3 1200 cycles per hour
Rated Insulation Voltage ( $U_i$ )	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V
Rated Impulse Withstand Voltage ( $U_{imp}$ )	6 kV
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage ( $U_c$ )	50 Hz 24 ... 60 V 50 Hz / 60 Hz 24 ... 60 V 60 Hz 24 ... 60 V DC Operation 20 ... 60 V
Operate Time	Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms
Connecting Capacity Main Circuit	Rigid 1/2x 2.5 ... 10 m <sup>2</sup> Flexible with Ferrule 1/2x 1.5 ... 10 m <sup>2</sup> Flexible with Insulated Ferrule 1x 1.5 ... 10 m <sup>2</sup> Flexible with Insulated Ferrule 2x 1.5 ... 4 m <sup>2</sup>
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 m <sup>2</sup> Flexible with Insulated Ferrule 1x 0.75 ... 2.5 m <sup>2</sup> Flexible with Insulated Ferrule 2x 0.75 ... 1.5 m <sup>2</sup> Rigid 1/2x 1 ... 2.5 m <sup>2</sup>
Wire Stripping Length	Control Circuit 10 mm Main Circuit 14 mm
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Terminal Type	Screw Terminals

## Dimensions

Product Net Width	45 mm
Product Net Depth / Length	86 mm
Product Net Height	86 mm
Product Net Weight	0.35 kg

## Popular Downloads

Instructions and Manuals	1SBC101027M6801
--------------------------	-----------------

---

## Ordering

---

Minimum Order Quantity

1 piece

Customs Tariff Number

85364900

---

---

## Categories

---

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

