

PRODUCT-DETAILS

A75-30-11 220-230V 50Hz / 230-240V 60Hz A75-30-11 220-230V 50Hz / 230-240V 60Hz Contactor



General Information

Extended Product Type	A75-30-11 220-230V 50Hz / 230-240V 60Hz
Product ID	1SBL411001R8011
EAN	3471522093806
Catalog Description	A75-30-11 220-230V 50Hz / 230-240V 60Hz Contactor
Long Description	A75 contactors are mainly used for controlling 3-phase motors and generally for controlling power circuits up to 690 V AC / 1000 V AC or 220 V DC. The contactors can also be used for many other applications such as isolation, capacitor switching, lighting. The A... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles and 2 built-in auxiliary contacts, front and side-mounted add-on auxiliary contact blocks - Control circuit: AC operated with laminated magnet circuit - Accessories: a wide range of accessories is available.

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529

Container Information

Package Level 1 Units	1 piece
-----------------------	---------

Package Level 1 Width	140 mm
Package Level 1 Depth / Length	146 mm
Package Level 1 Height	96 mm
Package Level 1 Gross Weight	1.2 kg
Package Level 1 EAN	3471522093806
Package Level 2 Units	box 20 piece
Package Level 2 Width	503 mm
Package Level 2 Depth / Length	153 mm
Package Level 2 Height	307 mm
Package Level 2 Gross Weight	24 kg
Package Level 3 Units	160 piece

Certificates and Declarations (Document Number)

ASEFA Certificate	ASEFA_15201
BV Certificate	BV_2634H07559E0
CB Certificate	CB_CN45324
CCC Certificate	CCC_2018010304129267 CCC_2008010309289461
CSA Certificate	CSA_1033838_LR056745
Declaration of Conformity - CE	1SBD250801U1000
DNV Certificate	DNV-GL_TAE00000TX
DNV GL Certificate	DNV-GL_TAE00000TX
EAC Certificate	EAC_RU C-FR ME77 B01010
Environmental Information	1SBD250010E1003
GOST Certificate	GOST_POCCFRME77B07175
Instructions and Manuals	FPTC407700P0003
LOVAG Certificate	LOVAG_FR01006a-FR01030
LR Certificate	LRS_9830011E4
RINA Certificate	RINA_ELE128713XG001
RMRS Certificate	RMRS_0507015250
RoHS Information	1SBD250801U1000
UL Certificate	UL_20120830-E312527-10-1
UL Listing Card	UL_E312527

Environmental

Ambient Air Temperature	Close to Contactor for Storage -60 ... +80 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +55 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +55 °C Close to Contactor without Thermal O/L Relay (Uc) -40 ... +70 °C
Climatic Withstand	acc. to IEC 60068-2-30 and 60068-2-11 - UTE C 63-100 specification II
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0

Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Standards	Devices complying with international standards IEC 947-1 / 947-4-1, and European standards EN 60 947-1 / 60 947-4-1. Electromagnetic compatibility (EMC) acc. to amendment A11 to IEC 947-1, EN 60 947-1 and amendment 2 to IEC 947-4-1
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Supply Circuit 50 60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-5-1, $q = 40\text{ °C}$ 16 A acc. to IEC 60947-4-1, Open Contactors $q = 40\text{ °C}$ 125 A
Rated Operational Current AC-1 (I_e)	(690 V) 40 °C 125 A (690 V) 55 °C 105 A (690 V) 70 °C 85 A
Rated Operational Current AC-3 (I_e)	(1000 V) 55 °C 28 A (220 / 230 / 240 V) 55 °C 75 A (380 / 400 V) 55 °C 75 A (415 V) 55 °C 72 A (440 V) 55 °C 70 A (500 V) 55 °C 65 A (690 V) 55 °C 46 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 22 KWT (380 / 400 V) 37 KWT (415 V) 40 KWT (440 V) 40 KWT (500 V) 45 KWT (690 V) 40 KWT
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I_e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I_e AC-3
Rated Operational Current AC-15 (I_e)	(220 / 240 V) 4 A (24 / 127 V) 6 A (380 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Short-Circuit Protective Devices	Auxiliary Circuit - gG Type Fuses 10 A gG Type Fuses 160 A
Maximum Breaking Capacity	$\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100\text{ A}$) at 440 V 1300 A $\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100\text{ A}$) at 690 V 630 A
Maximum Electrical Switching Frequency	AC-1 600 cycles per hour AC-2 / AC-4 150 cycles per hour AC-3 600 cycles per hour
Rated Operational Current DC-13 (I_e)	(125 V) 0.55 / 69 A (24 V) 6 / 144 A (250 V) 0.3 / 75 A (48 V) 2.8 / 134 A (72 V) 1 / 72 A
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage (U_c)	50 Hz 220 ... 230 V 60 Hz 230 ... 240 V
Coil Consumption	Average Holding Value 50 / 60 Hz 18 5.5 V·A Average Pull-in Value 50 Hz 190 V·A Average Pull-in Value 60 Hz 180 V·A
Operate Time	Between Coil De-energization and NC Contact Closing 7 ... 14 ms Between Coil De-energization and NO Contact Opening 4 ... 11 ms Between Coil Energization and NC Contact Opening 7 ... 22 ms Between Coil Energization and NO Contact Closing 8 ... 27 ms

Connecting Capacity Main Circuit	Flexible with Cable End 6 ... 16 mm ² Rigid Cable 6 ... 25 mm ²
Connecting Capacity Auxiliary Circuit	Flexible with Cable End 0.75 ... 2.5 mm ² Rigid Cable 1 ... 4 mm ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Connecting Terminals (delivered in open position) Main Poles	M 6 (+,-) pozidriv 2 screws with 1x (13 x 10 mm) connector
Terminal Type	Screw Terminals

Dimensions

Product Net Width	82 mm
Product Net Depth / Length	108 mm
Product Net Height	110 mm
Product Net Weight	1.2 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100122C0202_Ch02
Instructions and Manuals	FPTC407700P0003

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

