


PRODUCT-DETAILS

AF205-40-11-13

AF205-40-11-13 Contactor



General Information

Extended Product Type	AF205-40-11-13
Product ID	1SFL527102R1311
EAN	7320500503706
Catalog Description	AF205-40-11-13 Contactor
Long Description	A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, Bypass and Distribution application up to max 1000 V. Operated with wide control voltage range 100-250 V, 50/60 Hz and DC

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Norway)	4117785
E-Number (Sweden)	3210335

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	166 mm
Package Level 1 Depth / Length	238 mm
Package Level 1 Height	180 mm
Package Level 1 Gross Weight	3.9 kg
Package Level 1 EAN	7320500503706

Certificates and Declarations (Document Number)

ABS Certificate	14-LD1092198-PDA
BV Certificate	BV_36353_A0BV
CB Certificate	SE-82315
CCC Certificate	CQC_2014010304676685
cUL Certificate	20140925-E73397
Declaration of Conformity - CE	2CMT2015-005440
DNV GL Certificate	DNV_E-14043
EAC Certificate	9AKK107046A8618
Instructions and Manuals	N/A
LR Certificate	LR_14_70011(E1)
PRS Certificate	TE_2092_880423_16
RINA Certificate	ELE060313XG_002
RMRS Certificate	9AKK107045A6978
RoHS Information	2CMT2015-005440

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V
General Use Rating UL/CSA	(600 V AC) 250 A

Environmental

Ambient Air Temperature	Close to Contactor for Storage -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... +50 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +70 °C
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	4
Number of Main Contacts	0

NC

Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors $q = 40^\circ\text{C}$ 350 A
Rated Operational Current AC-1 (I_e)	(1000 V) 40°C 275 A (1000 V) 60°C 250 A (1000 V) 70°C 200 A (690 V) 40°C 350 A (690 V) 60°C 300 A (690 V) 70°C 240 A
Rated Operational Current AC-3 (I_e)	(220 / 230 / 240 V) 55°C 205 A (380 / 400 V) 55°C 205 A (415 V) 55°C 205 A (440 V) 55°C 205 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 55 KWT (380 / 400 V) 110 KWT (415 V) 110 KWT (440 V) 132 KWT
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I_e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I_e AC-3
Short-Circuit Protective Devices	gG Type Fuses 400 A
Rated Short-time Withstand Current (I_{cw})	at 40°C Ambient Temp, in Free Air, from a Cold State 10 s 1640 A at 40°C Ambient Temp, in Free Air, from a Cold State 15 min 350 A at 40°C Ambient Temp, in Free Air, from a Cold State 1 min 670 A at 40°C Ambient Temp, in Free Air, from a Cold State 1 s 2050 A at 40°C Ambient Temp, in Free Air, from a Cold State 30 s 947 A
Maximum Breaking Capacity	$\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 440 V 3500 A
Maximum Electrical Switching Frequency	AC-1 300 cycles per hour
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U_{imp})	Main Circuit 8 kV
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) $0.85 \times U_c$ Min. ... $1.1 \times U_c$ Max. (at $\theta \leq 70^\circ\text{C}$)
Rated Control Circuit Voltage (U_c)	50 Hz 100 ... 250 V 60 Hz 100 ... 250 V DC Operation 100 ... 250 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 7 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 7 V·A Holding at Max. Rated Control Circuit Voltage DC 2.5 W Pull-in at Max. Rated Control Circuit Voltage 50 Hz 220 V·A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 220 V·A Pull-in at Max. Rated Control Circuit Voltage DC 190 W
Operate Time	Between Coil De-energization and NO Contact Opening 45 ... 80 ms Between Coil Energization and NO Contact Closing 25 ... 60 ms

Connecting Capacity Main Circuit	Flexible 2 x 50 ... 95 mm Rigid Al-Cable 1 x 95 ... 185 m ² Rigid Cu-Cable 1 x 6 ... 150 m ²
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 2x 0.75 ... 2.5 Flexible with Insulated Ferrule 2x 0.75 ... 2.5 Flexible 2x0.75 ... 2.5 m ² Solid 2 x 1 ... 4 m ² Stranded 2 x 1 4 m ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Terminal Type	Main Circuit: Bars

Dimensions

Product Net Width	140 mm
Product Net Depth / Length	152.5 mm
Product Net Height	195.6 mm
Product Net Weight	3.3 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100192C0206
Instructions and Manuals	N/A

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

