


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2119370003](#)  
**Status:** **Active**  
**Overview:** Coeur CST High-Current Interconnect System  
**Description:** Coeur CST High-Current Male Header, Dual Row, 2 Circuits, 6.00mm Diameter, Screw Attach, Keying Option B, Blue

**Documents:**

[Drawing \(PDF\)](#) [Test Summary 2119410000-TS-000 \(PDF\)](#)  
[Product Specification 2119410000-PS-000 \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Application Specification 2119410000-AS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)



Series image - Reference only

**General**

Product Family PCB Headers  
 Series [211937](#)  
 Application Power, Wire-to-Board  
 Overview [Coeur CST High-Current Interconnect System](#)  
 Product Name Coeur CST  
 UPC 193264140558

**Physical**

Breakaway No  
 Circuits (Loaded) 2  
 Circuits (maximum) 2  
 Diameter 6.00mm  
 Durability (mating cycles max) 200  
 Glow-Wire Capable No  
 Keying to Mating Part Yes  
 Lock to Mating Part Yes  
 Material - Metal Copper Alloy  
 Material - Plating Mating Silver  
 Material - Plating Termination Silver  
 Material - Resin Polyester  
 Net Weight 42.935/g  
 Number of Rows 2  
 Orientation Vertical  
 Packaging Type Tray  
 Pitch - Mating Interface 19.06mm  
 Polarized to Mating Part Yes  
 Temperature Range - Operating -40° to +105°C  
 Termination Interface: Style Screw

**Electrical**

Current - Maximum per Contact 120.0A  
 Voltage - Maximum 300V

**Material Info**

**Reference - Drawing Numbers**

Application Specification 2119410000-AS-000  
 Product Specification 2119410000-PS-000  
 Sales Drawing 2119370000-SD-000  
 Test Summary 2119410000-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ECHA\_01\_2020 (16  
 January 2020

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[211937 Series](#)

**Mates With**

6.00mm Receptacle Crimp Housing [211942](#)