

Product Change Notification

To: _____

Issued by: Panasonic Corporation, Industrial Solutions Systems Company
 Device Solutions Business Division Yamaguchi Plant

Approval	Check	Design
H. Serikawa	T. Hayashida	K. Hashizaki

Product	Aluminum Electrolytic Capacitors Surface Mount Type EB series																																																																																																																														
Part number	EEVEB2C100Q, EEVEB2C330SQ, EEVEB2D100Q, EEVEB2D220SQ EEVEB2E100Q, EEVEB2V3R3Q, EEVEB2V4R7Q, EEVEB2G3R3Q EEVEB2G4R7Q, EEVEB2W2R2Q, EEVEB2W3R3Q, EEVEB2W4R7SQ																																																																																																																														
Revised category	< >Design < >Parts / Materials < >Inspection / Test <#>Others * Incorrect description in catalog																																																																																																																														
Contents	<p>Change of length (L) tolerance</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <thead> <tr> <th rowspan="2">Part No.</th> <th rowspan="2">Size code</th> <th colspan="2">Dimension " L "</th> </tr> <tr> <th>Old spec.</th> <th>New spec.</th> </tr> </thead> <tbody> <tr><td>EEVEB2C100Q</td><td>G13</td><td>13.5 +0.5/-0.5</td><td>13.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2C330SQ</td><td>H16</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2D100Q</td><td>G17</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2D220SQ</td><td>H16</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2E100Q</td><td>G17</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2V3R3Q</td><td>G13</td><td>13.5 +0.5/-0.5</td><td>13.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2V4R7Q</td><td>G17</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2G3R3Q</td><td>G13</td><td>13.5 +0.5/-0.5</td><td>13.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2G4R7Q</td><td>G17</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2W2R2Q</td><td>G13</td><td>13.5 +0.5/-0.5</td><td>13.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2W3R3Q</td><td>G17</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> <tr><td>EEVEB2W4R7SQ</td><td>H16</td><td>16.5 +0.5/-0.5</td><td>16.5 +0.5/-1.0</td></tr> </tbody> </table> <div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Dimensions</p> </div> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center; font-size: small;"> <thead> <tr> <th>Size code</th> <th>φD</th> <th>L</th> <th>B</th> <th>H</th> <th>I</th> <th>W</th> <th>P</th> <th>K</th> </tr> </thead> <tbody> <tr><td>G13</td><td>10.0</td><td>13.5^{+0.5}_{-1.0}</td><td>10.3</td><td>12.0 max.</td><td>3.5</td><td>0.9±0.2</td><td>4.6</td><td>0.70±0.20</td></tr> <tr><td>G17</td><td>10.0</td><td>16.5^{+0.5}_{-1.0}</td><td>10.3</td><td>12.0 max.</td><td>3.5</td><td>0.9±0.2</td><td>4.6</td><td>0.70±0.20</td></tr> <tr><td>H16</td><td>12.0</td><td>16.5^{+0.5}_{-1.0}</td><td>13.5</td><td>15.0 max.</td><td>4.7</td><td>0.9±0.3</td><td>4.4</td><td>0.70±0.30</td></tr> <tr><td>J16</td><td>16.0</td><td>16.5^{+0.5}_{-1.0}</td><td>17.0</td><td>19.0 max.</td><td>5.5</td><td>1.2±0.3</td><td>6.7</td><td>0.70±0.30</td></tr> <tr><td>J21</td><td>16.0</td><td>21.5±0.5</td><td>17.0</td><td>19.0 max.</td><td>5.5</td><td>1.2±0.3</td><td>6.7</td><td>0.70±0.30</td></tr> <tr><td>K16</td><td>18.0</td><td>16.5±0.5</td><td>19.0</td><td>21.0 max.</td><td>6.7</td><td>1.2±0.3</td><td>6.7</td><td>0.70±0.30</td></tr> <tr><td>K21</td><td>18.0</td><td>21.5±0.5</td><td>19.0</td><td>21.0 max.</td><td>6.7</td><td>1.2±0.3</td><td>6.7</td><td>0.70±0.30</td></tr> </tbody> </table> </div> <p style="font-size: x-small; text-align: center;">*The dimensions of the vibration-proof products, please refer to the page of the mounting specification.</p>	Part No.	Size code	Dimension " L "		Old spec.	New spec.	EEVEB2C100Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0	EEVEB2C330SQ	H16	16.5 +0.5/-0.5	16.5 +0.5/-1.0	EEVEB2D100Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0	EEVEB2D220SQ	H16	16.5 +0.5/-0.5	16.5 +0.5/-1.0	EEVEB2E100Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0	EEVEB2V3R3Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0	EEVEB2V4R7Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0	EEVEB2G3R3Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0	EEVEB2G4R7Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0	EEVEB2W2R2Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0	EEVEB2W3R3Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0	EEVEB2W4R7SQ	H16	16.5 +0.5/-0.5	16.5 +0.5/-1.0	Size code	φD	L	B	H	I	W	P	K	G13	10.0	13.5 ^{+0.5} _{-1.0}	10.3	12.0 max.	3.5	0.9±0.2	4.6	0.70±0.20	G17	10.0	16.5 ^{+0.5} _{-1.0}	10.3	12.0 max.	3.5	0.9±0.2	4.6	0.70±0.20	H16	12.0	16.5 ^{+0.5} _{-1.0}	13.5	15.0 max.	4.7	0.9±0.3	4.4	0.70±0.30	J16	16.0	16.5 ^{+0.5} _{-1.0}	17.0	19.0 max.	5.5	1.2±0.3	6.7	0.70±0.30	J21	16.0	21.5±0.5	17.0	19.0 max.	5.5	1.2±0.3	6.7	0.70±0.30	K16	18.0	16.5±0.5	19.0	21.0 max.	6.7	1.2±0.3	6.7	0.70±0.30	K21	18.0	21.5±0.5	19.0	21.0 max.	6.7	1.2±0.3	6.7	0.70±0.30
Part No.	Size code			Dimension " L "																																																																																																																											
		Old spec.	New spec.																																																																																																																												
EEVEB2C100Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0																																																																																																																												
EEVEB2C330SQ	H16	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
EEVEB2D100Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
EEVEB2D220SQ	H16	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
EEVEB2E100Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
EEVEB2V3R3Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0																																																																																																																												
EEVEB2V4R7Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
EEVEB2G3R3Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0																																																																																																																												
EEVEB2G4R7Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
EEVEB2W2R2Q	G13	13.5 +0.5/-0.5	13.5 +0.5/-1.0																																																																																																																												
EEVEB2W3R3Q	G17	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
EEVEB2W4R7SQ	H16	16.5 +0.5/-0.5	16.5 +0.5/-1.0																																																																																																																												
Size code	φD	L	B	H	I	W	P	K																																																																																																																							
G13	10.0	13.5 ^{+0.5} _{-1.0}	10.3	12.0 max.	3.5	0.9±0.2	4.6	0.70±0.20																																																																																																																							
G17	10.0	16.5 ^{+0.5} _{-1.0}	10.3	12.0 max.	3.5	0.9±0.2	4.6	0.70±0.20																																																																																																																							
H16	12.0	16.5 ^{+0.5} _{-1.0}	13.5	15.0 max.	4.7	0.9±0.3	4.4	0.70±0.30																																																																																																																							
J16	16.0	16.5 ^{+0.5} _{-1.0}	17.0	19.0 max.	5.5	1.2±0.3	6.7	0.70±0.30																																																																																																																							
J21	16.0	21.5±0.5	17.0	19.0 max.	5.5	1.2±0.3	6.7	0.70±0.30																																																																																																																							
K16	18.0	16.5±0.5	19.0	21.0 max.	6.7	1.2±0.3	6.7	0.70±0.30																																																																																																																							
K21	18.0	21.5±0.5	19.0	21.0 max.	6.7	1.2±0.3	6.7	0.70±0.30																																																																																																																							
Attached Documents																																																																																																																															

Reply

Date / /

As the result of consideration, we will

Accepted/ Accepted but some conditions are needed/ Rejected/ Pending/ Proposing an alternative plan
--

Condition for experiments or reason for our decision etc.

Signature	Receiving Dep.