## **Product datasheet** Characteristics

# VBD01

TeSys Vario - switch disconnector - 20 A - on





#### Main

IVIAIII	
Range	TeSys
Product name	TeSys VARIO
Device short name	VBD
Device application	Preventive maintenance
Product or component type	Switch disconnector
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Network type	DC
	AC
Control type	Rotary handle
Rotary handle mounting style	Direct
Handle colour	Black
Handle front plate colour	Black
Suitability for isolation	Yes

#### Complementary

Complementary		-
Rotary handle padlocking	1 to 3 padlocks 48 mm	- 0
Marking	0 - 1	_ t
Mounting support	Handle: door Switch: door	L state
Fixing mode	Hole with 22.5 mm for handle	2
[Ue] rated operational voltage	690 V AC 50/60 Hz	
[Uimp] rated impulse withstand voltage	8 kV	_ [
[Ith] conventional free air thermal current	20 A	- S
[Ithe] conventional enclosed thermal current	16 A	_ remission

[le] rated operational current	11 A AC-23 Ue: 400 V
Rated operational power in W	11 kW at 690 V (AC-23A) 3 kW at 230240 V (AC-3) 4 kW at 400415 V (AC-3) 5.5 kW at 500 V (AC-3) 7.5 kW at 500 V (AC-23A) 7.5 kW at 690 V (AC-3) 4 kW at 230240 V (AC-23A) 5.5 kW at 400415 V (AC-23A)
Intermittent duty class	30
Making capacity ( I Rms)	200 A at 400 V AC-21A 200 A at 400 V AC-22A 200 A at 400 V AC-23A
[lcm] rated short-circuit making capacity	1 kA at 400 V at Ipeak
[lcw] rated short-time withstand Rms current	300 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 kA at 400 V - associated fuse 20 A aM 10 kA at 400 V - associated fuse 20 A gG
Breaking capacity	200 A at 400 V (AC-21A) 200 A at 400 V (AC-22A) 200 A at 400 V (AC-23A)
Device composition	Switch Handle
Mechanical durability	100000 cycles
Electrical durability	100000 cycles AC-21 30000 cycles DC-15
Connections - terminals	Power circuit: screw clamp terminals10 mm² - solid Power circuit: screw clamp terminals6 mm² - flexible - with cable end
Tightening torque	Power circuit: 2.1 N.m - on screw clamp terminals
Handle front plate dimension	60 x 60 mm
Height	74 mm
Width	60 mm
Net weight	0.215 kg

### Environment

IEC 60947-3	
ifications CCC	
CSA	
GL	
UL	
eatment TC	
protection IP20 conforming to IEC 60529	
IP65	
robustness Vibrations 10150 Hz (1 gn) c	conforming to IEC 60068-2-6
Shocks 11 ms (30 Gn) conform	ning to IEC 60068-2-27
temperature for operation -2050 °C	
nce 960 °C conforming to IEC 606	95-2-1
Shocks 11 ms (30 Gn) conform temperature for operation -2050 °C	ning to IEC 60068-2-27

## Offer Sustainability

Sustainable offer status	Green Premium product	
REACh free of SVHC	Yes	
EU RoHS Directive	Compliant EU RoHS Declaration	
Toxic heavy metal free	Yes	
Mercury free	Yes	
RoHS exemption information	Yes	
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months