Product datasheet Characteristics

VCF4

TeSys Vario - emergency stop switch disconnector - 80 A - on door





Main

Range	TeSys	
Product name	TeSys VARIO	<u> </u>
Device short name	VCF	
Product or component type	Emergency stop switch disconnector	, <u>, , , , , , , , , , , , , , , , , , </u>
Performance level	High performance	
Poles description	3P	
Contacts type and composition	3 NO	
Network type	DC AC	inio osii
Control type	Rotary handle	
Rotary handle mounting style	Direct	Ş
Handle colour	Red	-
Handle front plate colour	Yellow	9
Suitability for isolation	Yes	

Complementary

Rotary handle padlocking	1 to 3 padlocks 48 mm	bstit
Marking	0 - 1	Sasi
Mounting support	Handle: door Switch: door	tended a
Fixing mode	By 4 screws for handle	not in
[Ue] rated operational voltage	690 V AC 50/60 Hz	l si uc
[Uimp] rated impulse withstand voltage	8 kV	ntatic
[lth] conventional free air thermal current	80 A	docume
[Ithe] conventional enclosed thermal current	63 A	mer: This
[le] rated operational current	57 A AC-23 Ue: 400 V	isclai

Rated operational power in W	18.5 kW at 690 V (AC-3)
	15 kW at 230240 V (AC-3)
	22 kW at 400415 V (AC-3)
	30 kW at 500 V (AC-3) 30 kW at 690 V (AC-23A)
	37 kW at 500 V (AC-23A)
	18.5 kW at 230240 V (AC-23A)
	30 kW at 400415 V (AC-23A)
Intermittent duty class	30
Making capacity (I Rms)	800 A at 400 V AC-21A
	800 A at 400 V AC-22A
	800 A at 400 V AC-23A
[lcm] rated short-circuit making capacity	2.1 kA at 400 V at Ipeak
[lcw] rated short-time withstand Rms current	960 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 kA at 400 V - associated fuse 80 A aM
	10 kA at 400 V - associated fuse 80 A gG
Breaking capacity	640 A at 400 V (AC-21A)
	640 A at 400 V (AC-22A)
	640 A at 400 V (AC-23A)
Device composition	Switch
	Handle
Mechanical durability	30000 cycles
Electrical durability	30000 cycles AC-21
	30000 cycles DC-15
Connections - terminals	Power circuit: screw clamp terminals25 mm² - solid
	Power circuit: screw clamp terminals16 mm² - flexible - with cable end
Tightening torque	Power circuit: 4 N.m - on screw clamp terminals
Handle front plate dimension	60 x 60 mm
Height	83 mm
Width	60 mm
Net weight	0.56 kg

Environment

Standards	IEC 60947-3
Product certifications	CCC
	GL
	UL
	CSA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
	IP65
Mechanical robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6
	Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-2050 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Offer Sustainability

Sustainable offer status	Green Premium product	
REACh free of SVHC	Yes	
EU RoHS Directive	Compliant EU RoHS Declaration	
Toxic heavy metal free	Yes	
Mercury free	Yes	
RoHS exemption information	Yes	
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	

Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Contractual warranty	
Warranty	18 months