

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild <a href="general-regarding-numbers-n

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer




NDP7060 / NDB7060 N-Channel Enhancement Mode Field Effect Transistor


General Description


These N-Channel enhancement mode power field effect transistors are produced using Fairchild's proprietary, high cell density, DMOS technology. This very high density process is especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulses in the avalanche and commutation modes. These devices are particularly suited for low voltage applications such as automotive, DC/DC converters, PWM motor controls, and other battery powered circuits where fast switching, low in-line power loss, and resistance to transients are needed.

Features

- \blacksquare 75A, 60V. $\mathrm{R_{DS(ON)}} = 0.013\Omega$ @ $\mathrm{V_{GS}} = 10\mathrm{V}.$
- Critical DC electrical parameters specified at elevated temperature.
- Rugged internal source-drain diode can eliminate the need for an external Zener diode transient suppressor.
- 175°C maximum junction temperature rating.
- High density cell design for extremely low R_{DS(ON)}.
- TO-220 and TO-263 (D²PAK) package for both through hole and surface mount applications.







Absolute Maximum Ratings T_c = 25°C unless otherwise noted

Symbol	Parameter	NDP7060	NDB7060	Units	
V _{DSS}	Drain-Source Voltage	ge 60		V	
V_{DGR}	Drain-Gate Voltage ($R_{GS} \le 1 \text{ M}\Omega$)	60		V	
V _{GSS}	Gate-Source Voltage - Continuous	±20		V	
	- Nonrepetitive (t _P < 50 μs)	±			
I _D	Drain Current - Continuous	7	75	А	
	- Pulsed	22	25		
P _D	Maximum Power Dissipation @ T _C = 25°C	15	150		
	Derate above 25°C	,	W/°C		
T _J ,T _{STG}	Operating and Storage Temperature Range	-65 to	°C		
T _L	Maximum lead temperature for soldering purposes, 1/8" from case for 5 seconds	27	275		

Symbol	Parameter	Conditions		Min	Тур	Max	Units
DRAIN-S	OURCE AVALANCHE RATINGS (Note 1)	·					
W _{DSS}	Single Pulse Drain-Source Avalanche Energy	$V_{DD} = 25 \text{ V}, I_{D} = 75 \text{ A}$				550	mJ
I _{AR}	Maximum Drain-Source Avalanche Curre	ent				75	Α
OFF CH	ARACTERISTICS						
BV _{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, I_{D} = 250 \mu\text{A}$		60			V
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 60 \text{ V}, V_{GS} = 0 \text{ V}$	T ₁ = 125°C			250 1	μA mA
I _{GSSF}	Gate - Body Leakage, Forward	V _{GS} = 20 V, V _{DS} = 0 V	[· j · · = · ·			100	nA
I _{GSSR}	Gate - Body Leakage, Reverse	$V_{GS} = -20 \text{ V}, V_{DS} = 0 \text{ V}$				-100	nA
ON CHAI	RACTERISTICS (Note 1)	,		•		•	
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 250 \mu\text{A}$		2	2.8	4	V
CO(u)			T _J = 125°C	1.4	2.1	3.6	
R _{DS(ON)}	Static Drain-Source On-Resistance	$V_{GS} = 10 \text{ V}, I_D = 40 \text{ A}$ $T_J = 125^{\circ}\text{C}$	1 -		0.01	0.013	Ω
				0.015	0.024]	
I _{D(on)}	On-State Drain Current	$V_{GS} = 10 \text{ V}, V_{DS} = 10 \text{ V}$		75			Α
g _{FS}	Forward Transconductance	$V_{DS} = 10 \text{ V}, I_{D} = 37.5 \text{ A}$		15	39		S
DYNAMI	C CHARACTERISTICS	·					
C _{iss}	Input Capacitance	$V_{DS} = 25 \text{ V}, V_{GS} = 0 \text{ V},$ f = 1.0 MHz			2960	3600	pF
C _{oss}	Output Capacitance				1130	1600	pF
C _{rss}	Reverse Transfer Capacitance				380	800	pF
	NG CHARACTERISTICS (Note 1)	-					
t _{D(on)}	Turn - On Delay Time	$V_{DD} = 30 \text{ V}, \ I_{D} = 75 \text{ A},$ $V_{GS} = 10 \text{ V}, R_{GEN} = 5 \Omega$			17	30	nS
t _r	Turn - On Rise Time				128	400	nS
t _{D(off)}	Turn - Off Delay Time				54	80	nS
t _r	Turn - Off Fall Time				90	200	nS
$\overline{Q_{g}}$	Total Gate Charge	$V_{DS} = 48 \text{ V},$ $I_{D} = 75 \text{ A}, \ V_{GS} = 10 \text{ V}$			100	115	nC
Q_{gs}	Gate-Source Charge				14.5		nC
Q_{gd}	Gate-Drain Charge				51		nC

Electrical Characteristics (T _c = 25°C unless otherwise noted)							
Symbol	Parameter	Conditions		Min	Тур	Max	Units
DRAIN-S	OURCE DIODE CHARACTERISTICS	•					
l _s	Maximum Continuos Drain-Source Diode Forward Current					75	Α
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current					225	Α
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0 V, I _S = 37.5 A (Note 1)			0.9	1.3	V
			T _J = 125°C		0.84	1.2	
t _{rr}	Reverse Recovery Time	$V_{GS} = 0 \text{ V}, I_F = 75 \text{ A}, dI_F/dt = 100 \text{ A/}_F$	JS	40	76	150	ns
I _m	Reverse Recovery Current			2	4.7	10	Α
THERMA	L CHARACTERISTICS	•					
R _{eJC}	Thermal Resistance, Junction-to-Case				1	°C/W	
R _{øJA}	Thermal Resistance, Junction-to-Ambient				62.5	°C/W	

Note: 1. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2.0%.

Typical Electrical Characteristics





Figure 1. On-Region Characteristics

Figure 2. On-Resistance Variation with Gate Voltage and Drain Current







Figure 3. On-Resistance Variation with Temperature

Figure 4. On-Resistance Variation with Drain Current and Temperature






Figure 5. Transfer Characteristics

Figure 6. Gate Threshold Variation with Temperature

Typical Electrical Characteristics (continued)




Figure 7. Breakdown Voltage Variation with Temperature




Figure 8. Body Diode Forward Voltage Variation with Current and Temperature




Figure 9. Capacitance Characteristics




Figure 10. Gate Charge Characteristics




Figure 11. Switching Test Circuit





Figure 12. Switching Waveforms

Typical Electrical Characteristics (continued)






Figure 13. Transconductance Variation with Drain Current and Temperature

Figure 14. Maximum Safe Operating Area




Figure 15. Transient Thermal Response Curve

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

FACT $^{\text{TM}}$ QFET $^{\text{TM}}$ FACT Quiet Series $^{\text{TM}}$ QS $^{\text{TM}}$

 $\begin{array}{lll} \mathsf{FAST}^{\circledast} & \mathsf{Quiet}\,\mathsf{Series^{\mathsf{TM}}} \\ \mathsf{FASTr^{\mathsf{TM}}} & \mathsf{SuperSOT^{\mathsf{TM}}\text{-}3} \\ \mathsf{GTO^{\mathsf{TM}}} & \mathsf{SuperSOT^{\mathsf{TM}}\text{-}6} \\ \mathsf{HiSeC^{\mathsf{TM}}} & \mathsf{SuperSOT^{\mathsf{TM}}\text{-}8} \\ \end{array}$

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and h

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative