MOSFET – Power, N-Channel, DPAK/IPAK 9.0 A, 60 V

Designed for low voltage, high speed switching applications in power supplies, converters and power motor controls and bridge circuits.

Features

- NVD Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

Typical Applications

- Power Supplies
- Converters
- Power Motor Controls
- Bridge Circuits

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

		-	
Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	60	Vdc
Drain-to-Gate Voltage (R_{GS} = 10 M Ω)	V _{DGR}	60	Vdc
Gate–to–Source Voltage – Continuous – Non–repetitive (t _p ≤10 ms)	V _{GS} V _{GS}	±20 ±30	Vdc
Drain Current – Continuous @ T _A = 25°C – Continuous @ T _A = 100°C – Single Pulse (t _p ≤ 10 μs)	I _D ID I _{DM}	9.0 3.0 27	Adc Apk
$\begin{array}{l} \mbox{Total Power Dissipation } @ T_A = 25^{\circ}\mbox{C} \\ \mbox{Derate above } 25^{\circ}\mbox{C} \\ \mbox{Total Power Dissipation } @ T_A = 25^{\circ}\mbox{C (Note 1)} \\ \mbox{Total Power Dissipation } @ T_A = 25^{\circ}\mbox{C (Note 2)} \\ \end{array}$	P _D	28.8 0.19 2.1 1.5	W W/°C W W
Operating and Storage Temperature Range	T _J , T _{stg}	-55 to 175	°C
Single Pulse Drain-to-Source Avalanche Energy – Starting $T_J = 25^{\circ}C$ ($V_{DD} = 25$ Vdc, $V_{GS} = 10$ Vdc, L = 1.0 mH, I _L (pk) = 7.75 A, $V_{DS} = 60$ Vdc)	E _{AS}	30	mJ
Thermal Resistance – Junction-to-Case – Junction-to-Ambient (Note 1) – Junction-to-Ambient (Note 2)	$f{R}_{ heta JC} \ f{R}_{ heta JA} \ f{R}_{ heta JA}$	5.2 71.4 100	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/8" from case for 10 seconds	ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. When surface mounted to an FR4 board using 0.5 sq in pad size.

When surface mounted to an FR4 board using minimum recommended pad size.



ON Semiconductor®

www.onsemi.com



* The Assembly Location code (A) is front side optional. In cases where the Assembly Location is stamped in the package, the front side assembly code may be blank.

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

NTD3055-150, NVD3055-150

ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise noted)

C	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS			•	-	•	
Drain-to-Source Breakdown Voltage (Note 3) ($V_{GS} = 0 \text{ Vdc}, I_D = 250 \mu \text{Adc}$) Temperature Coefficient (Positive)		V _{(BR)DSS}	60 -	70.2		Vdc mV/°C
Zero Gate Voltage Drain Current ($V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}$) ($V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, T_J = 150^{\circ}\text{C}$)		I _{DSS}			1.0 10	μAdc
Gate-Body Leakage Current	$(V_{GS} = \pm 20 \text{ Vdc}, \text{ V}_{DS} = 0 \text{ Vdc})$	I _{GSS}	-	-	±100	nAdc
ON CHARACTERISTICS (Not	e 3)					
Gate Threshold Voltage (Note $(V_{DS} = V_{GS}, I_D = 250 \mu Adc$ Threshold Temperature Coeff	V _{GS(th)}	2.0	3.0 6.4	4.0	Vdc mV/°C	
Static Drain-to-Source On-F $(V_{GS} = 10 \text{ Vdc}, I_D = 4.5 \text{ Ad})$	R _{DS(on)}	-	122	150	mΩ	
$\begin{array}{l} \mbox{Static Drain-to-Source On-V} \\ \mbox{(V}_{GS} = 10 \mbox{ Vdc}, \mbox{ I}_{D} = 9.0 \mbox{ Ad} \\ \mbox{(V}_{GS} = 10 \mbox{ Vdc}, \mbox{ I}_{D} = 4.5 \mbox{ Ad} \end{array}$	V _{DS(on)}		1.4 1.1	1.9 -	Vdc	
Forward Transconductance (I	Note 3) (V _{DS} = 7.0 Vdc, I _D = 6.0 Adc)	g fs	-	5.4	-	mhos
DYNAMIC CHARACTERISTIC	S					
Input Capacitance		C _{iss}	-	200	280	pF
Output Capacitance	(V _{DS} = 25 Vdc, V _{GS} = 0 Vdc, f = 1.0 MHz)	C _{oss}	-	70	100	
Transfer Capacitance		C _{rss}	-	26	40	
SWITCHING CHARACTERIS	TICS (Note 4)					
Turn-On Delay Time		t _{d(on)}	-	11.2	25	ns
Rise Time	(V _{DD} = 48 Vdc, I _D = 9.0 Adc, V _{GS} = 10 Vdc,	t _r	-	37.1	80	
Turn-Off Delay Time	$R_{\rm G} = 9.1 \ \Omega$) (Note 3)	t _{d(off)}	-	12.2	25	
Fall Time		t _f	-	23	50]
Gate Charge	$(V_{DS} = 48 \text{ Vdc}, I_D = 9.0 \text{ Adc}, V_{GS} = 10 \text{ Vdc}) \text{ (Note 3)}$	QT	-	7.1	15	nC
		Q ₁	-	1.7	-]
		Q ₂	-	3.5	-	
SOURCE-DRAIN DIODE CH	ARACTERISTICS					
Forward On-Voltage		V _{SD}		0.98 0.86	1.20 -	Vdc
Reverse Recovery Time		t _{rr}	-	28.9	-	ns
	(I _S = 9.0 Adc, V _{GS} = 0 Vdc, dI _S /dt = 100 A/µs) (Note 3)	t _a	-	21.6	-]
		t.	1	73		1

Reverse Recovery Stored Charge

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: Pulse Width \leq 300 µs, Duty Cycle \leq 2%.

t_b

 $\mathsf{Q}_{\mathsf{R}\mathsf{R}}$

_

_

7.3


0.036


_

_

μC

4. Switching characteristics are independent of operating junction temperatures.





NTD3055-150, NVD3055-150




Figure 13. Thermal Response


ORDERING INFORMATION

Device	Package	Shipping [†]	
NTD3055-150G	DPAK (Pb-Free)	75 Units / Rail	
NTD3055-150-1G	IPAK (Pb-Free)	75 Units / Rail	
NTD3055-150T4G	DPAK (Pb-Free)	2500 / Tape & Reel	
NTD3055-150T4H	DPAK (Halide-Free)	2500 / Tape & Reel	
NVD3055-150T4G*	DPAK (Pb-Free)	2500 / Tape & Reel	
NVD3055-150T4G-VF01	DPAK (Pb-Free)	2500 / Tape & Reel	

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NVD Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

PACKAGE DIMENSIONS




*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

- DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
 DATUMS A AND B ARE DETERMINED AT DATUM
- PLANE H. ODTIONAL MOLD FEATURE

	INCHES		MILLIN	IETERS	
DIM	MIN	MAX	MIN	MAX	
Α	0.086	0.094	2.18	2.38	
A1	0.000	0.005	0.00	0.13	
b	0.025	0.035	0.63	0.89	
b2	0.028	0.045	0.72	1.14	
b3	0.180	0.215	4.57	5.46	
С	0.018	0.024	0.46	0.61	
c2	0.018	0.024	0.46	0.61	
D	0.235	0.245	5.97	6.22	
Е	0.250	0.265	6.35	6.73	
е	0.090 BSC		2.29 BSC		
н	0.370	0.410	9.40	10.41	
L	0.055	0.070	1.40	1.78	
L1	0.114 REF		2.90 REF		
L2	0.020	BSC	0.51 BSC		
L3	0.035	0.050	0.89	1.27	
L4		0.040		1.01	
Z	0.155		3.93		

PACKAGE DIMENSIONS



IPAK CASE 369D ISSUE C

NOTES:

z

1. DIMENSIONING AND TOLERANCING PER ANSI Y14 5M 1982

ANSI Y14.5M, 1982. . CONTROLLING DIMENSION: INCH.

	INCHES		MILLIMETER	
DIM	MIN	MAX	MIN	MAX
Α	0.235	0.245	5.97	6.35
в	0.250	0.265	6.35	6.73
С	0.086	0.094	2.19	2.38
D	0.027	0.035	0.69	0.88
Е	0.018	0.023	0.46	0.58
F	0.037	0.045	0.94	1.14
G	0.090 BSC		2.29 BSC	
н	0.034	0.040	0.87	1.01
J	0.018	0.023	0.46	0.58
к	0.350	0.380	8.89	9.65
R	0.180	0.215	4.45	5.45
S	0.025	0.040	0.63	1.01
V	0.035	0.050	0.89	1.27
Z	0.155		3.93	

STYLE 2: PIN 1. GATE

2. DRAIN

SOURCE
 DRAIN

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor "Typical" parameters which may be provided in ON Semiconductor dates sheets and/or application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights or others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor hardles against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors h

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative