INDUCTORS

MLJ1005 type

DK

NFC circuit/inductors for standard circuits **Multilayer ferrite MLJ** series



FEATURES

O Response to large currents with newly-developed ferrite materials.

O Narrow tolerance response with high-accuracy multiple layers.

○ Significant reductions of high-frequency loss due to the adoption of low-loss materials.

○ Operating temperature range: -55 to +125°C

APPLICATION

ONFC circuits for devices such as smartphones and PCs, and power lines for electronic devices. O Application guides: Smart phones/tablets

PART NUMBER CONSTRUCTION

MLJ	1005	W	W R16		T	000
Series name	L×W×H dimensions 1.0×0.5×0.5 mm	Characteristics	Inductance (nH)	Inductance tolerance	Packaging style	Internal code

* The " riangle " of the Part Number contains the inductance tolerance code, J (±5%), K (±10%), or M (±20%).

CHARACTERISTICS SPECIFICATION TABLE

L		Q	L, Q measur conditions	ring	Self-resona frequency	nt	DC resistance	Rated current			Part No.
			Frequency	Current				Isat	Isat	Itemp	
(nH)	Tolerance	min.	(MHz)	(mA)	(MHz)min.	(MHz)typ.	(Ω)max.	(mA)max.	(mA)typ.	(mA)max.	
75	±5% ±10%	15	25	1.0	650	950	0.25	400	500	550	MLJ1005W75NJT000 MLJ1005W75NKT000
100	±5% ±10%	15	25	1.0	550	830	0.30	400	500	500	MLJ1005WR10JT000 MLJ1005WR10KT000
120	±5% ±10%	15	25	1.0	460	740	0.39	380	450	450	MLJ1005WR12JT000 MLJ1005WR12KT000
140	±5% ±10%	15	25	1.0	400	650	0.45	380	450	450	MLJ1005WR14JT000 MLJ1005WR14KT000
150	±5% ±10%	15	25	1.0	400	600	0.45	350	450	450	MLJ1005WR15JT000 MLJ1005WR15KT000
160	±5% ±10%	15	25	1.0	330	600	0.52	350	450	400	MLJ1005WR16JT000 MLJ1005WR16KT000
180	±5% ±10%	15	25	1.0	320	570	0.58	300	370	400	MLJ1005WR18JT000 MLJ1005WR18KT000
220	±5% ±10%	15	25	1.0	290	500	0.58	300	370	400	MLJ1005WR22JT000 MLJ1005WR22KT000
270	±5% ±10%	15	25	1.0	260	450	0.65	280	350	350	MLJ1005WR27JT000 MLJ1005WR27KT000
330	±5% ±10%	15	25	1.0	230	380	0.65	230	300	350	MLJ1005WR33JT000 MLJ1005WR33KT000

Measurement equipment

Measurement item	Product No.	Manufacturer
L, Q	4294A+16034G	Keysight Technologies
Self-resonant frequency	E4991A	Keysight Technologies
DC resistance	Type-7561	Yokogawa

* Equivalent measurement equipment may be used.



Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (1/5)

MLJ1005 type

CHARACTERISTICS SPECIFICATION TABLE

L		Q	L, Q measu conditions	ring	Self-resona frequency	nt	DC resistance	Rated current			Part No.
			Frequency	Current				Isat	Isat	Itemp	
(nH)	Tolerance	min.	(MHz)	(mA)	(MHz)min.	(MHz)typ.	(Ω)max.	(mA)typ.	(mA)max.	(mA)max.	
390	±5%	15	25	1.0	210	330	0.97	230	300	300	MLJ1005WR39JT000
390	±10%	15	25	1.0	210	550	0.97	230	300	300	MLJ1005WR39KT000
470	±5%	15	25 1.0	1.0	190	300	0.97	200	250	300	MLJ1005WR47JT000
470	±10%	15 25		190	300 0.97 200	200 250	300	MLJ1005WR47KT000			
560	±5%	15	25	1.0	170	250	1.40	200	250	250	MLJ1005WR56JT000
500	±10%	13	20	1.0	170	200	1.40	200	200 2	200	MLJ1005WR56KT000

Measurement equipment


Measurement item	Product No.	Manufacturer
L, Q	4294A+16034G	Keysight Technologies
Self-resonant frequency	E4991A	Keysight Technologies
DC resistance	Type-7561	Yokogawa

* Equivalent measurement equipment may be used.

INDUCTORS


MLJ1005 type

L FREQUENCY CHARACTERISTICS



Measurement equipment				
Product No.	Manufacturer			
4294A+16034G Keysight Technologies				
* Equivalent measurement equipment may be used.				

Q FREQUENCY CHARACTERISTICS




* Equivalent measurement equipment may be used.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (3/5) Please note that the contents may change without any prior notice due to reasons such as upgrading.


MLJ1005 type

SHAPE & DIMENSIONS




Dimensions in mm


PACKAGING STYLE




Dimensions in mm

TAPE DIMENSIONS







PACKAGE QUANTITY Package quantity

10000 pcs/reel

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range	Storage temperature range*	Individual weight			
-55 to +125 °C	–55 to +125 °C	1.2 mg			
The storage temporature range is for after the assembly					


* The storage temperature range is for after the assembly.

RECOMMENDED LAND PATTERN



Dimensions in mm

RECOMMENDED REFLOW PROFILE



A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/5) Please note that the contents may change without any prior notice due to reasons such as upgrading.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

 The storage period is less than 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. 					
Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).					
Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.					
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.					
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.					
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.					
 Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference. 					
\bigcirc Use a wrist band to discharge static electricity in your body through t	he grounding wire.				
\bigcirc Do not expose the products to magnets or magnetic fields.					
O Do not use for a purpose outside of the contents regulated in the deli	ivery specifications.				
 The products listed on this catalog are intended for use in general ment, home appliances, amusement equipment, computer equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements ity require a more stringent level of safety or reliability, or whose failuperson or property. If you intend to use the products in the applications listed below or if set forth in the each catalog, please contact us. 	ent, personal equipment, office equipment, measurement equip- s of the applications listed below, whose performance and/or qual- ire, malfunction or trouble could cause serious damage to society,				
(1) Aerospace/aviation equipment(8) Public information-processing equipment(2) Transportation equipment (cars, electric trains, ships, etc.)(9) Military equipment(3) Medical equipment(10) Electric heating apparatus, burning equipment(4) Power-generation control equipment(11) Disaster prevention/crime prevention equipment(5) Atomic energy-related equipment(12) Safety equipment(6) Seabed equipment(13) Other applications that are not considered general-purpose applications(7) Transportation control equipment even for general-purpose applications, you are kindly requested to take into consideration securing pro					
tection circuit/device or providing backup circuits in your equipment.	, you are kindly requested to take into consideration security pro-				

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (5/5) Please note that the contents may change without any prior notice due to reasons such as upgrading.