# MOSFET – Power, Single N-Channel 60 V, 6.1 m $\Omega$ , 71 A

#### **Features**

- Small Footprint (5x6 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- NVMFS5C670NLWF Wettable Flank Option for Enhanced Optical Inspection
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

## **MAXIMUM RATINGS** (T<sub>J</sub> = 25°C unless otherwise noted)

,						
Parameter		Symbol	Value	Unit		
Drain-to-Source Voltage			V <sub>DSS</sub>	60	V	
Gate-to-Source Voltage	Э		$V_{GS}$	±20	V	
Continuous Drain		T <sub>C</sub> = 25°C	I <sub>D</sub>	71	Α	
Current $R_{\theta JC}$ (Notes 1, 3)	Steady	T <sub>C</sub> = 100°C		50		
Power Dissipation	State	T <sub>C</sub> = 25°C	$P_{D}$	61	W	
R <sub>θJC</sub> (Note 1)		T <sub>C</sub> = 100°C		31		
Continuous Drain		T <sub>A</sub> = 25°C	I <sub>D</sub>	17	Α	
Current R <sub>0JA</sub> (Notes 1, 2, 3)	Steady State	T <sub>A</sub> = 100°C	1	12		
Power Dissipation		T <sub>A</sub> = 25°C	$P_{D}$	3.6	W	
R <sub>θJA</sub> (Notes 1 & 2)		T <sub>A</sub> = 100°C		1.8		
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \mu s$		I <sub>DM</sub>	440	Α	
Operating Junction and Storage Temperature		T <sub>J</sub> , T <sub>stg</sub>	-55 to + 175	°C		
Source Current (Body Diode)		I <sub>S</sub>	68	Α		
Single Pulse Drain-to-Source Avalanche Energy ( $I_{L(pk)} = 3.6 \text{ A}$ )		E <sub>AS</sub>	166	mJ		
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		TL	260	°C		

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	2.4	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	41	


- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm<sup>2</sup>, 2 oz. Cu pad.
- 3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.




#### ON Semiconductor®

#### www.onsemi.com

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
60 V	6.1 mΩ @ 10 V	71 A
00 V	8.8 mΩ @ 4.5 V	717





XXXXXX = 5C670L

(NVMFS5C670NL) or

670LWF (NVMFS5C670NLWF)

= Assembly Location

Y = Year
W = Work Week

ZZ = Lot Traceability

#### **ORDERING INFORMATION**

See detailed ordering, marking and shipping information on page 5 of this data sheet.

# **ELECTRICAL CHARACTERISTICS** ( $T_J = 25^{\circ}C$ unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS	-						
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> / T <sub>J</sub>				27		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>GS</sub> = 0 V,	T <sub>J</sub> = 25 °C			10	
		V <sub>DS</sub> = 60 V	T <sub>J</sub> = 125°C			250	μΑ
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V				100	nA
ON CHARACTERISTICS (Note 4)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_{D} = 53 \mu A$		1.2		2.0	V
Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>				-4.7		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 35 A		5.1	6.1	mΩ
		V <sub>GS</sub> = 4.5 V	I <sub>D</sub> = 35 A		7.0	8.8	
Forward Transconductance	9 <sub>F</sub> s	V <sub>DS</sub> = 15 V, I <sub>D</sub> = 35 A			82		S
CHARGES AND CAPACITANCES	•						
Input Capacitance	C <sub>ISS</sub>	V <sub>GS</sub> = 0 V, f = 1 MHz, V <sub>DS</sub> = 25 V			1400		pF
Output Capacitance	Coss				690		
Reverse Transfer Capacitance	C <sub>RSS</sub>				15		
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> = 48 V; I <sub>D</sub> = 35 A			9.0		nC
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 48 V; I <sub>D</sub> = 35 A			20		nC
Threshold Gate Charge	Q <sub>G(TH)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 48 V; I <sub>D</sub> = 35 A			2.5		nC
Gate-to-Source Charge	Q <sub>GS</sub>				4.5		
Gate-to-Drain Charge	$Q_{GD}$				2.0		
Plateau Voltage	V <sub>GP</sub>				3.1		V
SWITCHING CHARACTERISTICS (Note 5	j)				•	•	•
Turn-On Delay Time	t <sub>d(ON)</sub>				11		
Rise Time	t <sub>r</sub>	$V_{GS}$ = 4.5 V, $V_{DS}$ = 48 V, $I_{D}$ = 35 A, $R_{G}$ = 2.5 $\Omega$			60		- ns
Turn-Off Delay Time	t <sub>d(OFF)</sub>				15		
Fall Time	t <sub>f</sub>				4		
DRAIN-SOURCE DIODE CHARACTERIS	TICS			I			
Forward Diode Voltage	$V_{SD}$	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 35 A	T <sub>J</sub> = 25°C		0.9	1.2	
			T <sub>J</sub> = 125°C		0.8		V
Reverse Recovery Time	t <sub>RR</sub>	$V_{GS} = 0 \text{ V, } dI_{S}/d_{t} = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 35 \text{ A}$			34		ns
Charge Time	ta				17		
Discharge Time	t <sub>b</sub>				17		
Reverse Recovery Charge	Q <sub>RR</sub>				19		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width  $\leq 300~\mu s$ , duty cycle  $\leq 2\%$ .

5. Switching characteristics are independent of operating junction temperatures.

#### **TYPICAL CHARACTERISTICS**




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On–Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current vs. Voltage

#### **TYPICAL CHARACTERISTICS**




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

#### **TYPICAL CHARACTERISTICS**





Figure 13. Thermal Characteristics

#### **DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>	
NVMFS5C670NLT1G	5C670L	DFN5 (Pb-Free)	1500 / Tape & Reel	
NVMFS5C670NLWFT1G	670LWF	DFN5 (Pb-Free, Wettable Flanks)	1500 / Tape & Reel	
NVMFS5C670NLT3G	5C670L	DFN5 (Pb-Free)	5000 / Tape & Reel	
NVMFS5C670NLWFT3G	670LWF	DFN5 (Pb-Free, Wettable Flanks)	5000 / Tape & Reel	
NVMFS5C670NLAFT1G	5C670L	DFN5 (Pb-Free)	1500 / Tape & Reel	
NVMFS5C670NLWFAFT1G	670LWF	DFN5 (Pb-Free, Wettable Flanks)	1500 / Tape & Reel	
NVMFS5C670NLWFAFT3G	670LWF	DFN5 (Pb-Free, Wettable Flanks)	5000 / Tape & Reel	

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### PACKAGE DIMENSIONS



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and the IIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regard

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative