



Kvaser D-sub 9 pin 120 Ohm termination adapter



Kvaser D-sub 9 pin 120 Ohm termination adapter

EAN: 73-30130-00801-4

Kvaser D-sub 9 pin 120 Ohm termination adapter is a CAN adaptor with a 9-pin male D-Sub connector at one end and a 9-pin female D-Sub socket at the other. Between CAN High (pin 7) and CAN Low (pin 2) there is a built-in 120 Ohm CAN terminating resistor.

This adapter provides quick and easy termination to any Kvaser high-speed CAN product. The Kvaser CAN termination adapter is used when there is a need to terminate a CAN node without internal termination or when no CAN node is connected to the bus. The Kvaser D-sub 9 pin 120 Ohm termination adapter has a 9-pin male D-Sub plug connector and a 9-pin female D-Sub socket. A 120 ohm terminating resistor sits between pins 2 and 7.



Kvaser D-sub 9 pin 120 Ohm termination adapter

TECHNICAL DATA - KVASER D-SUB 9 PIN 120 OHM TERMINATION ADAPTER	
PIN COUNT	N/A
PROMOTIONAL_TEXT	D-Sub 9
PC INTERFACE	Cable
SILENT MODE	N/A
CASING MATERIAL	N/A
ERROR COUNTERS READING	N/A
CERTIFICATIONS	CE,RoHS
PRODUCT GROUPS	Accessory
CAN FD	No
ERROR COUNTERS READING	No
ON-BOARD BUFFER	No
OPERATING SYSTEM	Win XP, Linux, Win 7, Win Vista, Win 10, Win 8
CERTIFICATIONS	CE, RoHS
CONNECTOR	DSUB 9
CURRENT CONSUMPTION	N/A
HEIGHT (MM)	N/A
OPERATING TEMPERATURE RANGE (C)	-30.00 to 85.00
MAXIMUM BITRATE (KBPS)	N/A
CASING MATERIAL	N/A
CB BOARD	No
STATUS	Active
ON-BOARD TX BUFFER	No
CLOCK SYNC	No
PROMOTIONAL_TEXT	9-pin male-to-female D-Sub connector with termination.
NETWORK CHANNEL(S)	

Kvaser
Aminogatan 25 A SE 431 53 Mölndal SWEDEN
Kvaser Europe AB
Telephone: +46 31 886344
Email: sales@kvaser.com
<https://www.kvaser.com/>



Kvaser D-sub 9 pin 120 Ohm termination adapter

ERROR FRAME GENERATION	No
MINIMUM BITRATE (KBPS)	N/A
CONNECTOR	DSUB 9
API, LICENCED	None
API, LICENCED	
MSGRATE RX MAX	N/A
WIDTH (MM)	N/A
TIMESTAMP RESOLUTION (US)	N/A
WEIGHT (G)	9.0
MSGRATE TX MAX	N/A
CB BOARD	No
TIMESTAMP RESOLUTION (US)	N/A
ON-BOARD RX BUFFER	N/A
STATUS	Active
RUGGED	N/A
IP CLASS	
ON-BOARD BUFFER	N/A
DATABASE DBC SUPPORT	No
API, FREE	N/A
NETWORK CHANNEL(S)	
OPERATING SYSTEM	Win XP, Linux, Win 7, Win Vista, Win 10, Win 8
ERROR FRAME DETECTION	No
ON-BOARD RX BUFFER	No
EMBEDDED SCRIPT	No
ON-BOARD TX BUFFER	N/A
SOUND	No
PRODUCT GROUPS	Accessory
ERROR FRAME DETECTION	N/A

Kvaser
Aminogatan 25 A SE 431 53 Mölndal SWEDEN
Kvaser Europe AB
Telephone: +46 31 886344
Email: sales@kvaser.com
<https://www.kvaser.com/>



Kvaser D-sub 9 pin 120 Ohm termination adapter

RUGGED	No
OPERATING TEMPERATURE RANGE (C)	-30.00 to 85.00
GALVANIC ISOLATION	No
SOUND	N/A
CLOCK SYNC	N/A
ERROR FRAME GENERATION	N/A
LENGTH (MM)	N/A
# OF CAN CHANNELS	0
API, FREE	
PC INTERFACE	Cable
PIN COUNT	N/A
PRODUCT GROUP	N/A
# OF CAN CHANNELS	0
MINIMUM BITRATE (KBPS)	N/A
SILENT MODE	No
EMBEDDED SCRIPT	No
GALVANIC ISOLATION	N/A
HEIGHT (MM)	N/A
MAXIMUM BITRATE (KBPS)	N/A
CURRENT CONSUMPTION	
CAN FD	No
WEIGHT (G)	N/A
MSGRATE RX MAX	N/A
MSGRATE TX MAX	N/A
IP CLASS	N/A

The information herein is subject to change without notice