



3.5 HARD DRIVE DATA SHEET

Smart. Safe. Secure.
Surveillance-Specialised Storage



SkyHawk™ leverages Seagate's extensive experience in designing drives purpose-built for surveillance applications.



Best-Fit Applications

- Network video recorders (NVR)
- Surveillance DVRs



SKYHAWK
HEALTH

Key Advantages

ImagePerfect™ firmware is designed to ensure seamless video footage capture in 24x7 surveillance workloads¹ that record video from 64 HD cameras.

SkyHawk Health Management actively helps protect your surveillance storage by focusing on prevention, intervention, and recovery options.² Included is RAID RapidRebuild™, which provides 3x faster volume rebuilds over traditional RAID rebuilds.

RV sensors built in allow drives to maintain performance in multi-bay systems, giving customers the flexibility to scale their systems when more storage is needed.

ATA streaming support enables recordings from up to 64 HD cameras for smooth, uninterrupted footage.

1 M hours MTBF, 3-year limited warranty³ represents an improved total cost of ownership (TCO) with reduced maintenance costs.

Lower power consumption means a reduction in heat emissions, which improves reliability in surveillance solutions. Tarnish-resistant components help protect drive from environmental elements, increasing field reliability.

Unparalleled data protection with an optional 2-year Rescue Data Recovery Services plan, providing access to Seagate's secure labs with industry-leading data recovery success rates.

¹ SkyHawk surveillance drives are designed for always-on workloads of 180 TB/year. For higher transaction workloads, see Seagate's enterprise-class drive offerings.

² Contact your Seagate sales representative for further information.

³ Seagate does not recommend operating at sustained extreme temperatures. Operating at higher temperatures will reduce the useful life of the products.



Specifications	8 TB	8 TB	6 TB	6 TB	4 TB
Standard Model Numbers ¹	ST8000VX004	ST8000VX0022	ST6000VX001	ST6000VX0023	ST4000VX005
SkyHawk™ Health Management Included	Yes	Yes	Yes	Yes	Yes
Interface	SATA 6 Gb/s	SATA 6Gb/s	SATA 6 Gb/s	SATA 6 Gb/s	SATA 6 Gb/s
Features and Performance					
Drive Bays Supported	Up to 16	Up to 16	Up to 16	Up to 16	Up to 16
Cameras Supported	Up to 64	Up to 64	Up to 64	Up to 64	Up to 64
RV Sensors	Yes	Yes	Yes	Yes	Yes
Max Sustained Transfer Rate OD (MB/s)	210MB/s	210MB/s	180MB/s	195MB/s	180MB/s
Cache (MB)	256	256	256	256	256
Reliability/Data Integrity					
Tarnish Resistant	Yes	Yes	Yes	Yes	Yes
Load/Unload Cycles	300,000	300,000	300,000	300,000	600,000
Non-recoverable Read Errors Rate, Max	1 per 10E15	1 per 10E15	1 per 10E14	1 per 10E15	1 per 10E14
Power-On Hours per year	8,760	8,760	8,760	8,760	8,760
Workload Rate Limit (WRL) ²	180	180	180	180	180
Mean Time Between Failures (MTBF) (hours)	1,000,000 hr	1,000,000 hr	1,000,000 hr	1,000,000 hr	1,000,000 hr
Warranty, Limited (years) ³	3	3	3	3	3
Power Management					
Startup Current, Typical (12V, A)	1.8	2	1.8	2	1.8
Average Operating Power (W)	8.73 W	9 W	5 W	9 W	3.7 W
Idling Average (W)	7.06 W	7.6 W	3.4 W	7.2 W	2.5 W
Standby Mode/Sleep Mode, Typical (W)	0.96/0.96	0.6/0.6	0.25/0.25	0.6/0.6	0.25/0.25
Voltage Tolerance (5 V)	+10/-5%	±5%	±5%	±5%	±5%
Voltage Tolerance (12 V)	±10%	±10%	±10%	±10%	±10%
Environmental/Temperature					
Operating (ambient, min °C)	5	5	0	5	0
Operating (drive case, max °C) ⁴	70	70	70	70	70
Non-operating (ambient, min °C)	-40	-40	-40	-40	-40
Physical					
Height (mm/in, max)	26.11 mm/1.028 in	26.11 mm/1.028 in	26.11 mm/1.028 in	26.11 mm/1.028 in	20.2 mm/0.795 in
Width (mm/in, max)	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in
Depth (mm/in, max)	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in
Weight (lb/g)	716 g/1.579 lb	780 g/1.72 lb	610 g/1.345 lb	705 g/1.55 lb	490 g/1.08 lb
Carton Unit Quantity	20	20	20	20	20
Cartons per Pallet / Cartons per Layer	40/8	40/8	40/8	40/8	40/8

1 Later 6 TB and 3 TB models are ST6000VX001 and ST3000VX009.

2 SkyHawk surveillance drives are designed for always-on workloads of 180 TB/year. For higher transaction workloads, see Seagate's enterprise-class drive offerings.

3 Extended warranty options available. Consult your distributor for details.

4 Seagate does not recommend operating at sustained extreme temperatures. Operating at higher temperatures will reduce useful life of the products.



Specifications	4 TB	3 TB	3 TB	2TB	2 TB
Standard Model Numbers ¹	ST4000VX007	ST3000VX009	ST3000VX010	ST2000VX012	ST2000VX008
SkyHawk™ Health Management Included	Yes	—	—	—	—
Interface	SATA 6 Gb/s	SATA 6Gb/s	SATA 6Gb/s	SATA 6Gb/s	SATA 6 Gb/s
Features and Performance					
Drive Bays Supported	Up to 16	Up to 8	Up to 8	Up to 8	Up to 8
Cameras Supported	Up to 64	Up to 64	Up to 64	Up to 64	Up to 64
RV Sensors	Yes	—	—	—	—
Max Sustained Transfer Rate OD (MB/s)	190MB/s	180MB/s	190MB/s	180MB/s	180MB/s
Cache (MB)	64	256	64	256	64
Reliability/Data Integrity					
Tarnish Resistant	Yes	Yes	Yes	Yes	Yes
Load/Unload Cycles	300,000	300,000	300,000	600,000	300,000
Non-recoverable Read Errors Rate, Max	1 per 10E14	1 per 10E14	1 per 10E14	1 per 10E14	1 per 10E14
Power-On Hours per year	8,760	8,760	8,760	8,760	8,760
Workload Rate Limit (WRL) ²	180	180	180	180	180
Mean Time Between Failures (MTBF) (hours)	1,000,000 hr	1,000,000 hr	1,000,000 hr	1,000,000 hr	1,000,000 hr
Warranty, Limited (years) ³	3	3	3	3	3
Power Management					
Startup Current, Typical (12V, A)	1.8	1.8	1.8	1.8	1.8
Average Operating Power (W)	5.5 W	3.5 W	5.6 W	3.7 W	5.6 W
Idling Average (W)	3.2 W	2.5 W	4 W	2.5 W	4 W
Standby Mode/Sleep Mode, Typical (W)	0.25/0.25	0.25/0.25	0.5/0.5	0.25/0.25	0.5/0.5
Voltage Tolerance (5 V)	±5%	±5%	±5%	±5%	±5%
Voltage Tolerance (12 V)	±10%	±10%	±10%	±10%	±10%
Environmental/Temperature					
Operating (ambient, min °C)	0	0	0	0	0
Operating (drive case, max °C) ⁴	70	70	70	70	70
Non-operating (ambient, min °C)	-40	-40	-40	-40	-40
Physical					
Height (mm/in, max)	26.11 mm/1.028 in	20.2 mm/0.795 in	26.11 mm/1.028 in	20.2 mm/0.795 in	26.11 mm/1.028 in
Width (mm/in, max)	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in	101.85 mm/4.01 in
Depth (mm/in, max)	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in	146.99 mm/5.787 in
Weight (lb/g)	635 g/1.4 lb	490 g/1.08 lb	490 g/1.08 lb	415 g/0.915 lb	610 g/1.345 lb
Carton Unit Quantity	20	25	20	20	20
Cartons per Pallet / Cartons per Layer	40/8	40/8	40/8	40/8	40/8

1 Later 6 TB and 3 TB models are ST6000VX001 and ST3000VX009.

2 SkyHawk surveillance drives are designed for always-on workloads of 180 TB/year. For higher transaction workloads, see Seagate's enterprise-class drive offerings.

3 Extended warranty options available. Consult your distributor for details.

4 Seagate does not recommend operating at sustained extreme temperatures. Operating at higher temperatures will reduce useful life of the products.



Specifications	1 TB
Standard Model Numbers ¹	ST1000VX005
SkyHawk™ Health Management Included	—
Interface	SATA 6 Gb/s
Features and Performance	
Drive Bays Supported	Up to 8
Cameras Supported	Up to 64
RV Sensors	—
Max Sustained Transfer Rate OD (MB/s)	180MB/s
Cache (MB)	64
Reliability/Data Integrity	
Tarnish Resistant	Yes
Load/Unload Cycles	—
Non-recoverable Read Errors Rate, Max	1 per 10E14
Power-On Hours per year	8,760
Workload Rate Limit (WRL) ²	180
Mean Time Between Failures (MTBF) (hours)	1,000,000 hr
Warranty, Limited (years) ³	3
Power Management	
Startup Current, Typical (12V, A)	1.8
Average Operating Power (W)	5.6 W
Idling Average (W)	4 W
Standby Mode/Sleep Mode, Typical (W)	0.5/0.5
Voltage Tolerance (5 V)	±5%
Voltage Tolerance (12 V)	±10%
Environmental/Temperature	
Operating (ambient, min °C)	0
Operating (drive case, max °C) ⁴	70
Non-operating (ambient, min °C)	-40
Physical	
Height (mm/in, max)	20.2 mm/0.795 in
Width (mm/in, max)	101.85 mm/4.01 in
Depth (mm/in, max)	146.99 mm/5.787 in
Weight (lb/g)	415 g/0.915 lb
Carton Unit Quantity	25
Cartons per Pallet / Cartons per Layer	40/8

1 Later 6 TB and 3 TB models are ST6000VX001 and ST3000VX009.

2 SkyHawk surveillance drives are designed for always-on workloads of 180 TB/year. For higher transaction workloads, see Seagate's enterprise-class drive offerings.

3 Extended warranty options available. Consult your distributor for details.

4 Seagate does not recommend operating at sustained extreme temperatures. Operating at higher temperatures will reduce useful life of the products.

seagate.com



© 2020 Seagate Technology LLC. All rights reserved. Seagate, Seagate Technology, and the Spiral logo are registered trademarks of Seagate Technology LLC in the United States and/or other countries. ImagePerfect, SkyHawk, and the SkyHawk logo are either trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. When referring to drive capacity, one gigabyte, or GB, equals one billion bytes; and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formatting and other functions, and thus will not be available for data storage. Quantitative usage examples for various applications are for illustrative purposes. Actual quantities will vary based on several factors, including file size, file format, features and application software. Actual data rates may vary depending on operating environment and other factors, such as chosen interface and disk capacity. Seagate reserves the right to change, without notice, product offerings or specifications. DS1902.13-2001GB January 2020