


**T30R****111-03011**

T18S – T250XL



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties, ensures a simple and quick installation. Whilst easily installed by hand, manual and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

For the routing, bundling and securing of cables, pipes and hoses.

**Base Data****Application Method**

Quick, simple fixing by hand or with HellermannTyton tensioning tools

**Colour**

Black (BK)

**Label E-Number Finland**

13 705 01

**Label E-Number Norway**

13 450 37

**Label E-Number Sweden**

15 160 64

**Package Content**

100

**Quantity per**

Bag

**Recommended Application Tool**

MK3SP, MK3PNSP2, MK7P, MK7, MK20

**Material and Specifications****Flammability**

UL94 V2

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Operating Temperature (Metric)**

-40 °C to +80 °C Continuous, (+105 °C for 500 h)

**Product Dimensions****Bundle Diameter max (Imperial)**

1.38 "

**Bundle Diameter max (Metric)**

35 mm

**Bundle Diameter min (Imperial)**

.06 "

**Bundle Diameter min (Metric)**

1.5 mm

**Length L (Imperial)**

5.9 "

**Length L (Metric)**

150 mm

**Minimum Tensile Strength (imperial)**

30

**Minimum Tensile Strength (N)**

135 N

**Width W (Imperial)**

.14 "

**Width W (Metric)**

3.5

© HellermannTyton 2006