

Short-circuit connector - SAC-5P-M12MS BK BR 1-2-4 - 1054366

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Termination plug for PSR-CT series RFID transponder switches, M12 male, 5-pos., closes the circuit at the last Y distributor in a series connection


Product Description

Blind plugs for each sensor circuit from the PSR-CT safety circuits.

Your advantages

- ✓ Easy installation with M12 connection
- ✓ Eliminates wiring errors
- ✓ Supports consistent field installation of the sensor circuit up to protection class IP67 or IP69K

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 698007
GTIN	4055626698007
Weight per Piece (excluding packing)	12.300 g
Custom tariff number	85332100
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug)
---------------------------------	-------------------------

General

Number of positions	5
Color handle area	black
Coding	A - standard
Overvoltage category	II
Degree of pollution	3
Insertion/withdrawal cycles	≥ 100

Short-circuit connector - SAC-5P-M12MS BK BR 1-2-4 - 1054366

Technical data

Material

Flammability rating according to UL 94	HB
--	----

Standards and Regulations


Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings


Dimensional drawing



Plug, M12 x 1, straight, shielded

Short-circuit connector - SAC-5P-M12MS BK BR 1-2-4 - 1054366

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

Classifications

eCl@ss

eCl@ss 6.0	27279200
eCl@ss 7.0	27279218
eCl@ss 9.0	27060311

ETIM

ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855