

## USB-C to VGA Vertical Adapter (M/F) - USB 3.1, Gen 1, Thunderbolt 3, 1920 x 1200 (1080p), 5 Gbps, Black

MODEL NUMBER: U444-000-VGA



USB Type-C to VGA converter connects a VGA monitor to your tablet, phone, MacBook, Chromebook or Ultrabook's USB-C or Thunderbolt 3 port.

### Features

#### USB Type-C to VGA Adapter Connects to Your Laptop or Tablet's USB-C or Thunderbolt 3 Port

This USB Type-C to VGA adapter connects a VGA monitor to the USB Type-C or Thunderbolt 3 port on your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone. It's an ideal connector for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen. It saves you money by allowing you to use your existing VGA display instead of buying a new monitor.

#### Supports USB Type-C DisplayPort Alternate Mode for Converting Video Signals

By connecting the USB Type-C plug to a source device that supports USB DisplayPort Alt Mode, you can output 1080p video to a VGA monitor, television or projector without the hassle of installing special software drivers.

#### Transmits Crystal-Clear 1080p Video to a VGA Display

To send high-definition video to a VGA television, projector or monitor, connect the VGA port to the display using a VGA cable (such as Tripp Lite's P500-Series, sold separately). The VGA port supports HD video resolutions up to 1920 x 1200 (1080p) at 60 Hz.

#### Vertical Molding Prevents Blockage of Adjacent Ports

The USB Type-C input's vertical orientation results in a slimmer adapter that maximizes space around the device's ports and prevents them from being blocked. Unlike traditional USB cables that connect in only one direction, the reversible USB Type-C male connector plugs into a USB Type-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

#### Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play USB Type-C to VGA adapter is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB Type-C or Thunderbolt 3 port. It requires no software, drivers or external power. The palm-sized one-piece molding fits into your pocket, briefcase or laptop bag for connecting to VGA displays anywhere.

### Highlights

- Vertical USB Type-C plug orientation prevents adjacent ports from being blocked
- Converts video signals from sources supporting USB Type-C DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Reversible USB Type-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect your laptop to a VGA monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the MacBook, Chromebook or laptop in your office or home workspace
- Stream online video or games from your computer on a larger VGA display

### System Requirements

- Source device with USB Type-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with VGA input

### Package Includes



- U444-000-VGA USB-C to VGA Vertical Adapter, M/F, Black
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332238115
INPUT	
Bus Powered	Yes
Product Length (in.)	2.53
Product Length (cm.)	6.5
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
PHYSICAL	
Color	Black
Material of Construction	PBT, ABS
Unit Dimensions (hwd / in.)	0.56 x 0.08 x 2.53
Unit Packaging Type	Polybag
Unit Weight (kg)	0.01
Unit Weight (lbs.)	0.020
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 104F (0 ~ 40C)
Storage Temperature Range	5 ~ 122F (-15 ~ 50C)
Relative Humidity	0 ~ 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1920 x 1080 (1080P) @ 60 Hz



USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	Stereo
Driver Required	No
USB Power Delivery (PD) Charging Support	No
Technology	USB 3.1 (Gen 1); VGA/SVGA
<b>SPECIAL FEATURES</b>	
HDR Support	No
<b>CERTIFICATIONS</b>	
Certifications	Tested to RoHS, REACH, CE and FCC
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>