

USB-C to VGA Adapter with Alternate Mode - DP 1.2, Right-Angle USB-C

MODEL NUMBER: U444-06N-VGA-RA



USB-C to VGA converter connects a VGA monitor to your tablet, MacBook, Chromebook, Ultrabook or smartphone's USB-C or Thunderbolt 3 port.

Features

Right-Angle USB-C to VGA Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 PortThis USB Type-C to VGA adapter connects a VGA monitor to the USB-C or Thunderbolt 3 port on your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone. It's an ideal connector for multitasking, presenting video at trade shows and conferences, editing documents, playing online games and watching movies on a larger screen. It saves you money by allowing you to use your existing VGA display instead of buying a new monitor.

Supports USB-C DisplayPort Alternate Mode for Transmitting Video SignalsBy connecting the USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 1080p video to a compatible monitor, television or projector without installing special software drivers.

Transmits Crystal-Clear 1080p Video to a VGA DisplayTo send high-definition video to a VGA television, projector or monitor, connect the VGA port to the display using a VGA cable (sold separately). The VGA port supports HD video resolutions up to 1920 x 1200 (1080p) at 60 Hz., as well as 24-bit Deep Color (8 bits per channel). The USB-C to VGA cable transfers data at rapid USB 3.1 Gen 1 speeds up to 5 Gbps.

Reversible USB-C Connector Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Right-Angle USB-C Plug Makes Connecting in Tight Spaces EasierThe space-saving right-angle USB-C plug is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Ready to Use Right from the Package, So You Can Plug and Play ImmediatelyThe plug-and-play USB Type-C to VGA cable requires no software or drivers to download and install. Just connect the right-angle USB-C plug to the USB-C or Thunderbolt 3 port on a source device that supports USB DisplayPort Alternate Mode. The six-inch adapter fits into your laptop bag, purse or briefcase for connecting to VGA displays anywhere. It's backward compatible with previous USB generations, so you can use it with legacy equipment.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Right-angle USB-C plug allows easier connection in confined or hard-to-reach spaces
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect your laptop to a VGA monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the MacBook, Chromebook or laptop in your office or home workspace
- Stream online video or games from your computer on a larger VGA display

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode (USB 3.1 Gen 1 compatibility required to achieve USB 3.1 Gen 1 speeds)



- Display device with VGA input

Package Includes

- U444-06N-VGA-RA Right-Angle USB-C to VGA Adapter, M/F, White
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332214195
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.2
Product Length (ft.)	0.5
Product Length (m.)	0.2
BATTERY	
Battery Charging (1.2 Port)	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
PHYSICAL	
Cable Jacket Rating	VW-1
Color	White
Material of Construction	PVC and ABS
Shipping Dimensions (hwd / in.)	0.85 x 4.00 x 4.80
Shipping Weight (kg)	0.05
Unit Dimensions (hwd / cm)	1.5 x 4.2 x 3.7
Unit Dimensions (hwd / in.)	0.6 x 1.6 x 1.5
Unit Packaging Type	Box



ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	2.9 BTU/Hr
Power Consumption (Watts)	0.85
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE) - RIGHT ANGLE
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1920 x 1200 (1080p) @60Hz
Displayport Specification	1.2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Max Supported Color Depth	24-bit True Color
Technology	USB; USB 3.1 (Gen 1); VGA/SVGA
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>