



Surface Mounted System

STS-K002L-G / STS-K002L-B

This speech transfer system features individual speaker and microphone units for the customer-side. This system also includes our open duplex amplifier, a hearing loop, and a free-standing staff microphone and speaker unit.

It is suitable for quiet environments with low ambient noise.

Components

- Speech Transfer Amplifier [STS-A31H]
- Surface Mounted Speaker and Microphone [STS-S60-G/B] [STS-M54-G/B]
- Staff Loudspeaker Unit [STS-SU1-G/B]
- PS-55 Power Supply [PS-55-01]
- Counter Hearing Loop Aerial [IL-AE99]

Physical Data (boxed)

Dimensions	Height – 130mm (5.11") Width – 340mm (13.38") Depth – 240mm (9.44")
Weight	2.90kg (6.39lbs)
Construction	Mild Steel
	ABS Plastic
Finish	Grey Powder Coated Leatherette
	Black Textured Powder Coated

Applications

For use where one to one communication takes place at a counter or booth with a security screen:

- Banks
- Post Offices
- Ticket Kiosks
- Information Centres
- Airports

Standards

- BS EN 60118-4 in correct installations
- CE, ROHS and WEEE compliant
- EN 55032:2015 compliant
- EN 55103-2:2009 compliant

Talk to us now:
+44 (0) 1732 223900 (UK & ROW)
+1 616 392 3400 (US & Canada)
www.contacta.co.uk

Physical and Technical Data (Individual Parts)

Component	Physical Data	Technical Data		
Speech Transfer Amplifier	Dimensions: Height - 116mm (4.57") Width - 115mm (4.53") Depth - 40mm (1.57") Weight: 100g (0.22lbs) Construction: ABS Plastic Finish: Matt Black Fine Texture	Supply Voltage	12-14 VDC	
		Quiescent Current	100mA typical	
		Operating Current	2A typical on speech peaks	
		Power Switch	Push on - push off (tact switch under membrane)	
		Microphones	Electret, supply 5V via 2.2K load resistor	
		Speaker Output Power	RMS: 2.5W / 8 Ω 4.4W / 4 Ω	
		Loop Drive Compliance	Constant current, bounded by 4V RMS & 2A RMS	
		Total Harmonic Distortion	<5% (loop and speakers)	
PS-55 Power Supply	Dimensions: Height - 93mm (3.66") Width - 49mm (1.93") Depth - 36mm (1.42") Cable length: 1.8m (70.87") Weight: 180g (0.39lbs) Construction: ABS Case Finish: Black	Input	100-240V 50-60Hz 1A max	
		Output	14V 2.14A 30W max	
Staff Loudspeaker Unit	Dimensions: Height - 70mm (2.76") Width - 100mm (3.94") Depth - 160mm (6.30") Weight: 850g (1.87lbs) Construction: Mild Steel Finish: Grey Powder Coated Leatherette Black Textured Powder Coated	RMS	5W	
		Impedance	4 Ω	
		Output	SPL 1W @ 1M 85dB	
		Frequency Response	150Hz - 10300Hz	
Surface Mounted Speaker and Microphone	Dimensions: Height - 75mm (2.95") Width - 60mm (2.36") Depth - 110mm (4.33") Weight: 550g (1.21lbs) Construction: Mild Steel Finish: Grey Powder Coated Leatherette Black Textured Powder Coated	Speaker	RMS	5W
			Impedance	4Ω
			Output	SPL 1W @ 1M 85dB
			Frequency Response	150Hz - 10300Hz
		Microphone	Directional Response	Omni-Directional
			Frequency Response	100Hz - 5000Hz
			Sensitivity	-42.5 ± 2.0dB @ 1KHz (0dB=1V/pa)
			Impedance	2K Ohms +/- @ 1KHz
Counter Hearing Loop Aerial	Dimensions: To be moulded on site to required size/ shape by installers. Weight: 100g (0.22lbs) Construction: Copper Wire with Black Protective Covering Finish: Black			