



⚠ Discontinued

LA1LC025 has not been replaced. Please contact your customer care center for more information.

Main

Range	TeSys
Device short name	LA1LC
Product or component type	Auxiliary contact

Complementary

Range compatibility	TeSys Integral contactor breaker
Mounting location	Right side
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NO + 1 NC contactor state 1 NO tripped
[Ui] rated insulation voltage	690 V
[Ith] conventional free air thermal current	6 A
Connections - terminals	screw clamp terminals 2 0.00 in ² (1.5 mm ²) screw clamp terminals 1 0.00 in ² (2.5 mm ²)
Net weight	0.37 lb(US) (0.17 kg)

Environment

Environmental characteristic	Standard environment
------------------------------	----------------------

Ordering and shipping details

Category	22384-STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	00785901545873
Returnability	No
Country of origin	CZ

Offer Sustainability

RECh Regulation	REACH Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------