

## Electronic housing - EMG150-LG/MSTB - 2907596

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Electronic housing, for PCB insertion, without screw connection terminal blocks and cover, with lateral opening for connector

### Your advantages

- ✓ Choice of four cover sizes in transparent or color versions
- ✓ Practical and easy-to-wire conductor connections
- ✓ Uniform and appropriate housing technology
- ✓ High degree of flexibility due to the wide choice of versions
- ✓ Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- ✓ User-friendly and safe mounting on DIN rails according to EN 60715
- ✓ Inflammability class V0 insulation material (according to UL 94)
- ✓ Shock and contamination-proof accommodation of electronic components
- ✓ Universal PCBs for all pitches

### Key Commercial Data

Packing unit	2 pc
Minimum order quantity	2 pc
GTIN	 4 017918 147877
GTIN	4017918147877
Weight per Piece (excluding packing)	107.900 g
Custom tariff number	85472000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### General

Housing type	Component housing
Housing material	Polycarbonate fiber reinforced
Color (RAL)	green

# Electronic housing - EMG150-LG/MSTB - 2907596

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Dimensions

Length	75 mm
Height	47.5 mm
Width	150 mm
Depth	75 mm

### Technical data

Power dissipation without gap	12.3 W
Power dissipation with 20 mm gap	13.1 W

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section flexible max.	2.5 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----


### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings


# Electronic housing - EMG150-LG/MSTB - 2907596

Dimensional drawing



1 = Top edge of the PCB  
B = Housing width

Dimensional drawing



## Electronic housing - EMG150-LG/MSTB - 2907596

### Classifications

#### eCl@ss

eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

#### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

### Approvals

#### Approvals

---

Approvals

EAC

---


Ex Approvals

---

#### Approval details

## Electronic housing - EMG150-LG/MSTB - 2907596

### Approvals

EAC		B.01742
-----	---	---------

### Accessories

#### Accessories

#### Device marking

Marking material - EMG-GKS 22 - 2941594



Device marking label, width: 22 mm, area: 22 x 8 mm, e.g. for EML(20x8) R adhesive marking material

Marking material - EMG-GKS 22 - 2941594



Device marking label, width: 22 mm, area: 22 x 8 mm, e.g. for EML(20x8) R adhesive marking material

### Filler plug

Electronic housing - EMG-KA - 2941510



Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.

Electronic housing - EMG-KA - 2941510



Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.

### PCB

## Electronic housing - EMG150-LG/MSTB - 2907596

### Accessories

Electronic housing - P 1-EMG150 - 2946049

PCB for assembling electronic components



Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

### Necessary add-on products

Covering hood - EMG150-H 7,5MM KLAR - 2943178



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm

Covering hood - EMG150-H 15MM KLAR - 2943165



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 150 mm

## Electronic housing - EMG150-LG/MSTB - 2907596

### Accessories

Electronic housing - EMG150-H 52MM GN - 2943521



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 150 mm