

Data sheet

Art.No.: 81.000.6332.0

Switched-mode power supply WIPOS PB1 12-2.75

wipos switched-mode power supply, nominal voltage: 12 V DC / 2,75 A, (setting range 12-14 V DC) sustained short-circuit protection, input voltage range: 90-264 V AC / 120-375 V DC, single phase, DIN rail mounted device 3 mod.



Art.No.	81.000.6332.0
EAN	4049088106170
Order Unit	1

Technical data

General

Connection type	Screw connection
Number of phases	Single phase power supply
Modular version	Yes
Mounting type, other	No
Mounting type, wall mounting	No
Rail mounting possible	Yes
Housing material	Plastic
Operating temperature min.	-40 °C
Operating temperature max.	71 °C
relative humidity min.	20 %
relative humidity max.	95 %
Storage temperature / transport min.	85 °C
Storage temperature / transport max.	-40 °C
Degree of protection (IP)	IP20
Pollution degree	2
Parallel-service possible	No

Technical data

Function display	"DC OK" LED grün (U(o) 9...10,8V)
function display "DC Low"	"DC LOW" LED rot (U(o) < 9...10,8V)
Short-circuit protective device	Strombegrenzung (fold forward)
temperature coefficient	±0,03%/K
ripple and noise	< 0.05 V
hold time 115V AC	> 20 ms
hold time 230V AC	> 100 ms
isolating voltage Output DC	4242 V
cohesive resistance (In-/Output)	100 MOhm
Derating	56°C...71°C: 2,5 %/K
cooling	free convection
MTBF	607.000h
Connector cross section (input)	min. 0,5mm ² (AWG24) max. 2,5mm ² (AWG12)

Connector cross section (output)	min. 0,5mm ² (AWG24) max. 2,5mm ² (AWG12)
Wire strip length	7 m
Permissible torque max.	0.6 Nm
Control "Adj"	trimming potentiometer for fine-tuning of U(out)
CE-Norm	EN61000-6-3, EN 55022 Class B, EN61000-3-2, EN61000-3-3, EN61000-6-2, EN55024, EN61000-4-2, Level 4, EN61000-4-3 Level 3, EN61000-4-4 Level 4, EN61000-4-5 L-N Level 3, L/N-FG Level 4, EN61000-4-6 Level 3, EN61000-4-8 Level 4, EN61000-4-11, ENV 50204 Level 2, EN61204-3
Approval cULus	UL 508 Listed, UL60950-1 Recognized
Number of +	2
Number of -	2
Further terminals	L, N

Output

Type of output voltage	DC
Power output	33 W
Output voltage stabilized	Yes
Output voltage	12 V
Min. output voltage	12 V
Max. output voltage	14 V
Min. output voltage	12 V
Max. output voltage	14 V
Output current	2.75 A

Input

Type of voltage (input voltage)	
Primary voltage range	90 V
Min. input voltage	90 V
Max. input voltage	264 V
Rated frequency min.	47 Hz
Rated frequency max.	63 Hz
Max. starting current	50 A
Input fuse	T2A / 250V (intern)
input protection	Varistor (voltage-sensitive resistor)



Dimensions

Depth	56.5 mm
Width	53 mm
Height	91 mm
Mounting Distance horizontal	25 mm
Mounting Distance vertical	25 mm
Weight	190 g

Classification

ECLASS 8.1	27049002
ETIM 7.0	EC002540
ETIM 6.0	EC002540
ETIM 5.0	EC002540
ETIM 3.0	EC001039

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Die Reproduktion, Distribution und Utilization of this document as well as the communication of its contents to others without express authorization is prohibited.



Qu - PEE 12/92

Teile-Nr. / Part-No.	Typ / Type
81.000.6320.0	wipos PB1 24-1,5
81.000.6332.0	wipos PB1 12-2,75

Weitere Angaben siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

ja/yes Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance		CAD-Zeichnung, keine manuellen Änderungen CAD-Drawing, no manual modifications allowed			1. Verwendung: First Use:		Blatt: Sheet:		
 Maßstab/Scale		Werkstoff/ Material		2016	Tag/ Date	Name		Zeichnung Nr./ Drawing No.	
				gezeichnet drawn	29.02.	Koetzner		T 81.000.6320.0 01K Maße in mm/Dimensions are in mm	
				geprüft checked					
				Normgepr. Stand. check					
		Datei/ File: 031511_01K.DCD			Ersatz für/ Replacement for:				
		 www.wieland-electric.com		Type		Benennung/ Title		Teilespezifikation / Component specification	
Index									
Datum/ Blatt Date/ Sheet									
Änderung/ Revision									