



2601B-PULSE System SourceMeter[®] 10 μ sec Pulser/SMU Instrument

PRODUCT FACTSHEET

2601B-PULSE System SourceMeter® 10µsec Pulser/SMU Instrument





Features

- Industry leading Source Measure Unit with PulseMeter™ technology for 10 A @ 10 V, 10 microsecond pulse output
- No tuning required for inductive loads up to 3 µH
- Dual 1 Megasample/sec digitizers for high speed I/V pulse measurements (Pulser function only)
- DC capability up to ±40 V @ ±1.0 A, 40 Watt
- TSP (Test Script Processing) technology embeds complete test programs inside the instrument for best-in-class system-level throughput


Benefits

- Make DC/Pulse voltage and current measurements with a single instrument
- Minimize device self-heating; minimize burned probe tips
- No tuning of pulse output to ensure pulse fidelity
- Remote test head is not required enabling greater space savings

Superior Current Pulse Output Performance at 10A @ 10V at 10µsec



Typical Pulse output with overshoot and 6.47 µsec rise time from a competitive SMU




2601B-PULSE output without overshoot and 1.4 µsec rise time using PulseMeter® technology.

Typical Applications


Ideal for current/voltage ((I/V) characterization and functional test of a wide range of today's modern electronics and devices, such as applications like:



VCSELs for LIDAR



VCSELs for Facial Recognition



Circuit Protection Device Testing



SSD Power Management Fault Detection



Wafer Level Reliability Test

2601B-PULSE System SourceMeter® 10µsec Pulser/SMU Instrument

Pulser Condensed Specifications

Current Specifications

Source		
Range	Programming Resolution	Accuracy (23°C ±5°C) 1 Year +/- (% setting + volts)
1A	100 µA	0.17 % + 1 mA
5A	100 µA	0.17 % + 1 mA
10A	100 µA	0.22 % + 1 mA

Measure		
Range	Display Resolution	Accuracy (23°C ±5°C) 1 Year +/- (% setting + volts)
1A	10 µA	0.12 % + 0.3 mA
5A	10 µA	0.12 % + 1 mA
10A	100 µA	0.12 % + 1 mA

Voltage Specifications

Measure		
Range	Display Resolution	Accuracy (23°C ±5°C) 1 Year +/- (% setting + volts)
5A	10 µV	0.05 % + 1 mV
10A	100 µV	0.05 % + 4 mV

Pulse Limits

+/- 10 A @ +/- 10V pulse (3% duty cycle)
+/- 3 A @ +/- 10V pulse (10% duty cycle)
+/- 1 A @ +/- 10V pulse (30% duty cycle)
+/- 500 mA @ +/- 10V pulse (60% duty cycle)
+/- 250 mA @ +/- 10V continuous



Refer to www.tektronix.com for additional product details, complete specifications, application notes, software, videos, product tours.



2601B-PULSE System SourceMeter® 10µsec Pulser/SMU Instrument

SMU DC Condensed Specifications

DC Voltage Specifications

Source				Measure		
Range	Max. DC Current	Programming Resolution	Accuracy (23°C ±5°C) 1 Year +/- (% setting + volts)	Default Display Resolution	Input Resistance	Accuracy (23°C ±5°C) 1 Year +/- (% reading + volts)
100mV	3A	5 µV	0.02 % + 250 µV	100 nV	> 10 GΩ	0.015 % + 150 µV
1 V	3A	50 µV	0.02 % + 400 µV	1 µV	> 10 GΩ	0.015 % + 200 µV
6 V	3A	50 µV	0.02 % + 1.8 mV	10 µV	> 10 GΩ	0.015 % + 1 mV
40 V	1A	500 µV	0.02 % + 12 mV	10 µV	> 10 GΩ	0.015 % + 8 mV

DC Current Specifications

Source				Measure		
Range	Max. Voltage	Programming Resolution	Accuracy (23°C ±5°C) 1 Year +/- (% setting + amps)	Default Display Resolution	Voltage Burden	Accuracy (23°C ±5°C) 1 Year +/- (% reading + amps)
100 nA	40V	2 pA	0.1 % + 100 pA	100 fA	< 1 mV	0.050 % + 100 pA
1 µA	40V	20 pA	0.03 % + 800 pA	1 pA	< 1 mV	0.025 % + 500 pA
10 µA	40V	200 pA	0.03 % + 5 nA	10 pA	< 1 mV	0.025 % + 1.5 nA
100 µA	40V	2 nA	0.03 % + 60 nA	100 pA	< 1 mV	0.020 % + 25 nA
1 mA	40V	20 nA	0.03 % + 300 nA	1 nA	< 1 mV	0.020 % + 200 nA
10 mA	40V	200 nA	0.03 % + 6 µA	10 nA	< 1 mV	0.020 % + 2.5 µA
100 mA	40V	2 µA	0.03 % + 30 µA	100 nA	< 1 mV	0.020 % + 20 µA
1 A	40V	20 µA	0.05 % + 1.8 mA	1 µA	< 1 mV	0.030 % + 1.5 mA
3 A	6V	20 µA	0.06 % + 4 mA	1 µA	< 1 mV	0.050 % + 3.5 mA
10 A	20V	200 µA	0.5 % + 40 mA	10 µA	< 1 mV	0.400 % + 25 mA (typ.)

- 10A range accessible only in SMU DC Pulse mode
- LXI, USB2.0, GPIB, LAN, TSP-Link® and digital I/O Interfaces are supported.
- USB 2.0 port (memory I/O) on front panel for data import/export and system upgrades

Refer to www.tektronix.com for additional product details, complete specifications, application notes, software, videos, product tours.

Ordering Information

2601B-PULSE System SourceMeter®
10 µsec Pulser / SMU
Instrument

Accessories Supplied

2601B-P-INT Interlock/Connector Board
7709-308A Digital I/O Connector
17469460X TSP-Link/Ethernet Cable
2601B-PULSE QuickStart Guide
Test Script Builder Software (www.tektronix.com)
KickStart Startup Software (www.tektronix.com)
LabVIEW and IVI Drivers (www.tektronix.com)
Manual Documentation (www.tektronix.com)

Recommended Accessories

2601B-PULSE-CA1 1.2 meter BNC to BNC 50 Ohm Cables set
2601B-PULSE-CA2 2 independent 3.0 meter 50 ohm BNC to BNC coax cables used for SHI and SLO. Required accessory for the 2601B-PULSE-CA3 cable set.
2601B-PULSE-CA3 3.0 meter 15 Ohm BNC to BNC cable kit. The 2601B-PULSE-CA2 option is required with this accessory.

Recommended Services

2601B-PULSE-3Y-EW
1-year factory warranty extended to 3 years from date of shipment

2601B-PULSE-5Y-EW
1-year factory warranty extended to 5 years from date of shipment



Tektronix[®]

The image features the Tektronix logo in white, bold, sans-serif font, centered horizontally. The logo consists of the word "Tektronix" with a registered trademark symbol (®) to its upper right. A blue diagonal line cuts through the letter "k". The background is a gradient of blue, with several abstract, overlapping geometric shapes in various shades of blue and cyan, including a large diagonal band and several parallel lines, creating a modern, technical aesthetic.

Find more valuable resources at [TEK.COM](https://www.tek.com)

Copyright © Tektronix. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks or registered trademarks of their respective companies.
021820 1KW-61658-0

