


# Type 3 surge protection base element - PLT-SEC-T3-BE-FM-PT - 2907929

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Base element for protective plugs from the PLT-SEC-...-UT/PT product series with remote indication contact.



## Key Commercial Data

Packing unit	10 pc
GTIN	 4 055626 257679
GTIN	4055626257679
Weight per Piece (excluding packing)	44.000 g
Custom tariff number	85363030
Country of origin	Germany

## Technical data

### Dimensions

Height	101 mm
Width	17.7 mm
Depth	51.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 Div.

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m (amsl (above mean sea level))
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	30g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (5 ... 500 Hz / 2.5 h / X, Y, Z)

# Type 3 surge protection base element - PLT-SEC-T3-BE-FM-PT - 2907929

## Technical data

### General

EN type	T2 / T3
IEC power supply system	TN-S
	TT
Number of ports	One
Mounting type	DIN rail: 35 mm
Color	light grey RAL 7035
	traffic grey A RAL 7042
Housing material	PA 6.6-FR 20 % GF
	PA 6.6-FR
Degree of pollution	2
Flammability rating according to UL 94	V-0
Type	DIN rail module, two-section, divisible
Number of positions	2
Surge protection fault message	Remote indication contact

### Protective circuit

Nominal voltage $U_N$	240 V AC (TN-S)
	240 V AC (TT)
Nominal frequency $f_N$	50 Hz (60 Hz)
Maximum continuous voltage $U_C$	264 V AC
Rated load current $I_L$	26 A (at 30 °C)
Short-circuit current rating $I_{SCCR}$	10 kA AC
Max. backup fuse with branch wiring	depends on the plug used
Maximum backup fuse for through wiring	25 A (gG / B / C)

### Additional technical data

Short-circuit current rating $I_{SCCR}$	max. 5 kA DC (depends on the plug used)
Maximum continuous voltage $U_C$	240 V DC

### Indicator/remote signaling

Switching function	PDT contact
Operating voltage	250 V AC
	125 V DC (200 mA DC)
Operating current	0.5 A AC
	0.5 A DC (75 V DC)
Connection method	Push-in connection
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section solid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section AWG	30 ... 12
Stripping length	10 mm

# Type 3 surge protection base element - PLT-SEC-T3-BE-FM-PT - 2907929

## Technical data

### Connection data

Connection method	Push-in connection
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section solid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section AWG	24 ... 12
Stripping length	10 mm

### Standards and Regulations


Standards/specifications	IEC 61643-11 2011
	EN 61643-11 2012

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings


Diagram




Nominal current depending on ambient temperature

# Type 3 surge protection base element - PLT-SEC-T3-BE-FM-PT - 2907929

Dimensional drawing



Circuit diagram



## Classifications

eCl@ss

eCl@ss 6.0	27130800
eCl@ss 7.0	27130803
eCl@ss 8.0	27130803
eCl@ss 9.0	27130803

ETIM

ETIM 5.0	EC000472
----------	----------

# Type 3 surge protection base element - PLT-SEC-T3-BE-FM-PT - 2907929

## Classifications

### ETIM

ETIM 6.0	EC000472
ETIM 7.0	EC000472

## Approvals

### Approvals

#### Approvals

DNV GL / CCA / KEMA-KEUR / IECCEB Scheme / EAC

#### Ex Approvals

### Approval details

DNV GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	TAE00002U7
--------	--	---	------------

CCA			NTR-NL 7676
-----	--	--	-------------

KEMA-KEUR		<a href="http://www.dekra-certification.com">http://www.dekra-certification.com</a>	71-103027
-----------	--	---	-----------

IECEE CB Scheme		<a href="http://www.iecee.org/">http://www.iecee.org/</a>	NL-51083
-----------------	--	---	----------

EAC			RU C-DE.A*30.B01561
-----	--	--	---------------------

## Accessories

### Additional products

## Type 3 surge protection base element - PLT-SEC-T3-BE-FM-PT - 2907929

### Accessories

Type 3 surge protection plug - PLT-SEC-T3-24-P-UT/PT - 2907920



Replacement plug for type 3 surge protection from the PLT-SEC-...-UT/PT product series. Nominal voltage 24 V.

---

Type 3 surge protection plug - PLT-SEC-T3-60-P-UT/PT - 2907921



Replacement plug for type 3 surge protection from the PLT-SEC-...-UT/PT product series. Nominal voltage 60 V.

---

Type 3 surge protection plug - PLT-SEC-T3-120-P-UT/PT - 2907922



Replacement plug for type 2/3 surge protection from the PLT-SEC-...-UT/PT product series. Nominal voltage 120 V.

---

Type 3 surge protection plug - PLT-SEC-T3-230-P-UT/PT - 2907923



Replacement plug for type 2/3 surge protection from the PLT-SEC-...-UT/PT product series. Nominal voltage 230 V.

---