

Reducing adapter - REDUC-M-KV-M25/M20 - 1647624

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Reducing adapter, material: Brass, nickel-plated, connecting thread: M25 x 1.5, color: silver, with O-ring

Product Description

Reduced M25 to M20



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 941529
GTIN	4017918941529
Weight per Piece (excluding packing)	17.850 g
Custom tariff number	74153300
Country of origin	Germany

Technical data

Dimensions

Length	10 mm
Length without connecting thread	3 mm
Connecting thread diameter	25 mm
Hexagon angular dimension	30 mm
Length of the connecting thread	7 mm

Ambient conditions

Degree of protection (IP)	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material	Brass, nickel-plated
Outer thread	M25

Reducing adapter - REDUC-M-KV-M25/M20 - 1647624

Technical data

General

Internal thread	M20
Torque	7.5 Nm ... 8 Nm
Color	silver

Standards and Regulations

Halogen-free	no
--------------	----


Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Reducing adapter - REDUC-M-KV-M25/M20 - 1647624

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27149100
eCl@ss 6.0	27149100
eCl@ss 7.0	27439207
eCl@ss 8.0	27149109
eCl@ss 9.0	27440201

Reducing adapter - REDUC-M-KV-M25/M20 - 1647624

Classifications

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938
ETIM 6.0	EC002309
ETIM 7.0	EC002309

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501