

Media module - FL SFP GT - 2989420

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Gigabit SFP module for transmission up to 100 m.

Product Description

SFP module with a data transmission speed of 1000 Mbps and a maximum transmission length of 100 m.



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 346122
GTIN	4046356346122
Weight per Piece (excluding packing)	33.400 g
Custom tariff number	85176200
Country of origin	Taiwan

Technical data

Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)

Interfaces

Interface	Ethernet (RJ45)
No. of ports	1 (RJ45 port)
Transmission physics	Copper
Transmission speed	1 Gbps
Transmission length	100 m (per segment)

Media module - FL SFP GT - 2989420

Technical data

Interfaces

Signal LEDs	depending on the Factoryline device
-------------	-------------------------------------

Function

Basic functions	SFP module as copper port
Status and diagnostic indicators	via a Factoryline device

Network expansion parameters

Maximum conductor length (twisted pair)	100 m
---	-------

Supply voltage

Supply voltage	3.3 V (via Factoryline switch)
Max. current consumption	375 mA
Current consumption	375 mA

General

Mounting type	Insert in SFP slot
Type AX	Factoryline devices with SFP slot
Net weight	33.4 g
Housing material	Metal

Classifications

eCl@ss

eCl@ss 10.0.1	19179290
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	27250500
eCl@ss 5.1	27250500
eCl@ss 6.0	27250500
eCl@ss 7.0	27250501
eCl@ss 8.0	27149249
eCl@ss 9.0	19179290

ETIM

ETIM 4.0	EC000734
ETIM 5.0	EC002609
ETIM 6.0	EC000310
ETIM 7.0	EC000310

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015

Media module - FL SFP GT - 2989420

Classifications

UNSPSC

UNSPSC 12.01	43201410
UNSPSC 13.2	26121650
UNSPSC 18.0	43222604
UNSPSC 19.0	43222604
UNSPSC 20.0	43222604
UNSPSC 21.0	43222604