

# Transition sleeve from hose to cable - WP-EC TPE HF 15,8 BK - 3240976


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End sleeves, transition sleeves, from hose to cable



## Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 50 pc   |
| Minimum order quantity               | 50 pc   |
| GTIN                                 | <br>4 046356 710947 |
| GTIN                                 | 4046356710947   |
| Weight per Piece (excluding packing) | 3.060 g   |
| Custom tariff number                 | 39174000  |
| Country of origin                    | Germany   |
| Note                                 | Made to Order (non-returnable)  |

## Technical data

### Dimensions

|                  |         |
|------------------|---------|
| Length (b)       | 36.5 mm |
| Diameter         | 15.8 mm |
| Outside diameter | 15.8 mm |

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Short-term temperature          | 150 °C            |

### General

|  |              |
|--|--------------|
| Color                                  | black        |
| Components                             | halogen-free |
| Flammability rating according to UL 94 | HB           |

# Transition sleeve from hose to cable - WP-EC TPE HF 15,8 BK - 3240976

## Technical data

### General

|          |     |
|----------|-----|
| Material | TPE |
|----------|-----|

### Standards and Regulations

|  |    |
|--|----|
| Connection in acc. with standard       | UL |
| Flammability rating according to UL 94 | HB |

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27430316 |
| eCl@ss 4.0    | 27141100 |
| eCl@ss 4.1    | 27141100 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27439210 |
| eCl@ss 8.0    | 27439210 |
| eCl@ss 9.0    | 27430316 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC002584 |
| ETIM 5.0 | EC000519 |
| ETIM 6.0 | EC000519 |
| ETIM 7.0 | EC000519 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121404 |
| UNSPSC 18.0   | 39121404 |
| UNSPSC 19.0   | 39121404 |
| UNSPSC 20.0   | 39121404 |
| UNSPSC 21.0   | 39121404 |

# Transition sleeve from hose to cable - WP-EC TPE HF 15,8 BK - 3240976

## Approvals

### Approvals

---

#### Approvals

UL Recognized

---

#### Ex Approvals

---

## Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>