



### Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX0FF
Control circuit type	AC at 50...400 Hz DC standard
[Uc] control circuit voltage	220...230 V AC 50...400 Hz 220...230 V DC
Average resistance	37.55 Ohm latching at 20 °C 5139 Ohm unlatching at 20 °C
Product compatibility	CR1F150
Operating time	35...40 ms latching 50...100 ms unlatching
Mechanical durability	1 Mcycles
Maximum operating rate	120 cyc/h 40 °C

### Complementary

Control circuit voltage limits	Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc
--------------------------------	--

### Environment

Net weight	0.44 kg
------------	---------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

**Contractual warranty**

Warranty	18 months
----------	-----------