



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D6
Control circuit type	AC at 50 Hz
[Uc] control circuit voltage	415 V AC 50 Hz
Average resistance	463 Ohm at 20 °C
Inductance of closed circuit	26 H
Product compatibility	LC1D95 LC1D80
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 60 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.3...0.6 Uc at 50/60 Hz (at <55 °C) Operational: 0.8...1.1 Uc at 50 Hz (at <55 °C) Operational: 0.85...1.1 Uc at 60 Hz (at <55 °C)
Inrush power in VA	200 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	20 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	6...10 W at 50/60 Hz

Environment

Ambient air temperature for operation	-5...60 °C
Net weight	0.28 kg

Contractual warranty

Warranty	18 months
----------	-----------