



## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1FX
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F780
Control circuit type	AC at 40...400 Hz
[Uc] control circuit voltage	220...240 V AC 40...400 Hz
Average resistance	19.5 Ohm inrush at 20 °C 920 Ohm holding at 20 °C
Inductance of closed circuit	0.82 H
Operating time	130...230 ms opening 40...80 ms closing
Mechanical durability	5 Mcycles
Maximum operating rate	600 cyc/h 55 °C

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational: 0.85...1.1 Uc 40...400 Hz (at 55 °C) Drop-out: 0.2...0.4 Uc 40...400 Hz (at 55 °C)
Inrush power in VA	2100 VA 40...400 Hz cos phi 0.9 (at 20 °C)
Hold-in power consumption in VA	50 VA 40...400 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	44 W at 40...400 Hz

## Environment

Ambient air temperature for operation	-5...55 °C
Net weight	3 kg
Quantity per set	Set of 2

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------