



## Main

Range	TeSys
Product or component type	Specific contactor coil
Device short name	LX9FJ
Range compatibility	TeSys F LC1F contactor TeSys F DR5TE rectifier
Product compatibility	DR5TE LC1F400
Control circuit type	AC at 40...400 Hz low consumption DC low consumption
[Uc] control circuit voltage	380...415 V AC 40...400 Hz 380...415 V DC
Average resistance	311 Ohm inrush at 20 °C 3011 Ohm holding at 20 °C
Inductance of closed circuit	15 H
Operating time	60 ms opening 50 ms closing
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 70 °C

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.3...0.5 Uc (at 55 °C)
Inrush power in VA	500 VA 40...400 Hz (at 20 °C)
Hold-in power consumption in VA	23 VA 40...400 Hz (at 20 °C)
Heat dissipation	11.4...13.9 W

## Environment

Ambient air temperature for operation	-5...55 °C
---------------------------------------	------------

Net weight	0.97 kg
------------	---------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------