

Measuring instrument - PSM-FO-POWERMETER - 2799539

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fiber optic measuring case, consisting of an optical power meter, F-SMA, B-FOC adapters, reference fibers and operating instructions

Your advantages

- ✓ Suitable for termination devices with and F-SMA, B-FOC (ST[®]) connection
- ✓ Measurement at SC-RJ and SC duplex connection using add-on set
- ✓ The power meter can be switched between the following wavelengths: 660 nm, 780 nm, and 850 nm
- ✓ Reference cables with polymer fibers, PCF fibers, and fiberglass

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 126735
GTIN	4017918126735
Weight per Piece (excluding packing)	1,535.100 g
Custom tariff number	90314990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27144440
eCl@ss 4.0	24010400

Measuring instrument - PSM-FO-POWERMETER - 2799539

Classifications

eCl@ss

eCl@ss 4.1	24010400
eCl@ss 5.0	19030300
eCl@ss 5.1	19030300
eCl@ss 6.0	27061800
eCl@ss 7.0	27061803
eCl@ss 8.0	27149249
eCl@ss 9.0	27144440

ETIM

ETIM 2.0	EC001125
ETIM 3.0	EC001125
ETIM 4.0	EC002609
ETIM 5.0	EC002609
ETIM 6.0	EC002609
ETIM 7.0	EC002609

UNSPSC

UNSPSC 6.01	26121607
UNSPSC 7.0901	26121607
UNSPSC 11	26121607
UNSPSC 12.01	26121607
UNSPSC 13.2	26121650
UNSPSC 18.0	26121650
UNSPSC 19.0	26121650
UNSPSC 20.0	26121650
UNSPSC 21.0	26121650

Approvals

Approvals

Approvals


EAC

Ex Approvals

Approval details

Measuring instrument - PSM-FO-POWERMETER - 2799539

Approvals

EAC		RU *- DE.A*30.B.01628
-----	---	--------------------------

Accessories

Accessories

Measuring device adapter - PSM-FO-POWERMETER SCRJ-SET - 2901560



Powermeter supplementary set for devices with SC-RJ interface, consisting of one-meter polymer reference fiber (SC Simplex connector to F-SMA connector), one-meter of PCF-GI reference fiber (SC Simplex connector to B-FOC (ST[®]) connector) and SC-RJ coupling

Additional products

Measuring device adapter - PSM-FO-POWERMETER SCRJ-SET - 2901560



Powermeter supplementary set for devices with SC-RJ interface, consisting of one-meter polymer reference fiber (SC Simplex connector to F-SMA connector), one-meter of PCF-GI reference fiber (SC Simplex connector to B-FOC (ST[®]) connector) and SC-RJ coupling