

Media module - FL IF 2PSE-F - 2832904

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Interface module for connecting PoE twisted pair ports, RJ45, connection direction forward

Your advantages

- Suitable for GHS system
- IEEE 802.3af



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356076050
Weight per Piece (excluding packing)	70.000 g
Custom tariff number	85176200
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Caption	The figure shows a version of the interface module with the head station FL SWITCH MM HS
Width	31 mm
Height	84.7 mm
Depth	75.5 mm

Ambient conditions

Degree of protection	IP20
----------------------	------

Media module - FL IF 2PSE-F - 2832904

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Interfaces

Interface	Ethernet
No. of ports	2 (PoE ports)
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps (connection direction forwards)
Transmission length	100 m (per segment)

Function

Basic functions	Media module for Modular Managed Switch with Power over Ethernet IEEE802.3af, Power Source Equipment (PSE)
-----------------	--

Supply voltage

Supply voltage	Internal / 48 V DC for PoE
Supply voltage range	45.5 V DC ... 53 V DC
Typical current consumption	10 mA (max. 900 mA)

General

Mounting type	In the host system
Type AX	Block design
Net weight	70 g
Housing material	PA 6.6

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Operation: 25g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Storage/Transport: 50g, 11 ms duration, semi-sinusoidal shock impulse
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	Operation/Storage/Transport: 5g, 150 Hz, Criterion 3
Type of test	Free fall in acc. with IEC 60068-2-32
Test result	1 m
Noise emission	EN 61000-6-3/-4
Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Free from substances that could impair the application of coating	In acc. with VW specification
Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

Media module - FL IF 2PSE-F - 2832904

Technical data

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170390
eCl@ss 8.0	19170390
eCl@ss 9.0	19170390

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC001467
ETIM 5.0	EC000309
ETIM 6.0	EC000309
ETIM 7.0	EC000309

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410
UNSPSC 18.0	43223108
UNSPSC 19.0	43223108
UNSPSC 20.0	43223108
UNSPSC 21.0	43223108

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Media module - FL IF 2PSE-F - 2832904

Approvals

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
---------------	--	---	---------------

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
----------------	--	---	---------------

cULus Recognized			
------------------	--	--	--

Accessories

Accessories

Data cable by the meter

Network cable - FL CAT5 HEAVY - 2744814



CAT5-SF/UTP cable (J-02YS(ST)C HP 2 x 2 x 24 AWG), heavy-duty installation cable, 2 x 2 x 0.22 mm², solid conductor, shielded, outer sheath: 7.8 mm diameter, inner sheath: 5.75 mm ± 0.15 mm diameter

Network cable - FL CAT5 FLEX - 2744830



CAT5-SF/UTP cable (J-LI02YS(ST)C H 2 x 2 x 26 AWG), light-duty, flexible installation cable 2 x 2 x 0.14 mm², stranded, shielded, outer sheath: 5.75 mm ± 0.15 mm diameter

Plug

Media module - FL IF 2PSE-F - 2832904

Accessories

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.

RJ45 connector - FL PLUG RJ45 GN/2 - 2744571



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.

Power supply

Power supply unit - STEP-PS/ 1AC/48DC/2 - 2868680



Primary-switched STEP POWER power supply for DIN rail mounting, input: 1-phase, output: 48 V DC/2 A

Power supply unit - TRIO-PS/1AC/48DC/ 5 - 2866491



Primary-switched TRIO POWER power supply for DIN rail mounting, input: 1-phase, output: 48 V DC/5 A

Power supply unit - QUINT-PS/1AC/48DC/ 5 - 2866679



Primary-switched QUINT POWER power supply for DIN rail mounting with SFB (Selective Fuse Breaking) Technology, input: 1-phase, output: 48 V DC/5 A

Sleeve housings

Media module - FL IF 2PSE-F - 2832904

Accessories

RJ45 sleeve housings - VS-08-T-G-RJ45/IP20 - 1652295



RJ45 sleeve housing, IP20, for pin insert VS-08-ST-RJ45, with push-pull interlocking for panel mounting frames, inverted design, for Factoryline modular managed switches, for cable cross section 5.0 mm ... 6.5 mm

Terminal marking

Zack Marker strip, flat - ZBF 29:UNBEDRUCKT - 0829003



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into flat marker groove, for terminal block width: 29 mm, lettering field size: 29 x 6.4 mm, Number of individual labels: 3

Assembly tool - FL CRIMPTOOL - 2744869



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site