RG174 Coaxial Cable



Construction

Item	Material	Diameter	
		(Inch)	(mm)
Inner Conductor	Bare Copper	7/0.0063 ±0.001	7/0.16 ±0.03
Dielectric	Solid PE	0.06 ±0.003	1.52 ±0.08
Shield	90% Tinned Copper Braid	0.079 ±0.004	2 ±0.1
Jacket	PVC	0.11 ±0.005	2.8 ±0.13

Electrical Characteristics

Impedance : 50Ω ±2Ω Capacitance : 101pF/m Velocity of Propagation : 66% Max. Operating Frequency : 1GHz Max. Operating Voltage : 1500VRMS Corona Extinction Voltage : 1500VRMS Voltage Withstand : 2000VRMS Spark Test : 2000VRMS Operating Temp. Range : -40°C to +85°C

Attenuation (@20°C)

Frequency (MHz)	Attenuation (dB/100ft)	Attenuation (dB/100m)
50	6.4	21
100	9.8	32
200	14.6	48
400	21.3	70
600	25.9	85
860	32	105
1000	38.1	125

Part Number Table

Description	Length	Part Number
Coaxial Cable, RG174, PVC, Black	Per Meter or 100 Meter	RG174

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

