

# Program / configuration memory - SD FLASH 512MB APPLIC A - 2701799

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Program and configuration memory for extending the internal Flash memory, plug-in, 512 MB, with license key for function block libraries, e.g., for: SNMP, SQL, wireless, motion functions, etc.

Similar figure

## Product Description

Program and configuration memory for storing the application programs and other files in the file system of the PLC. A license key for activating further function block libraries is also included. Individual function blocks from Phoenix Contact, such as those from the SQL and SNMP library or Resy+, are licensed. This means that a fee is charged for each controller on which licensed function blocks are used. The blocks check the license stored on the controller during runtime and enable themselves or run for a limited time in demo mode.

Examples of licensed function blocks:

- Basic control functions for PID controllers with delay time constant in the D component
- Data transfer between the controller and SQL database with event-driven access to tables by means of SQL communication and Data Manipulation Language (DML)
- IT library for sending e-mails with the SMTP function, with DHCP client, DNS, and an FTP client function
- Secure, event-oriented, and inexpensive monitoring of all distributed plants via Ethernet as well as via serial interfaces


Observe the specified performance data of your controller(s) and check that it/they are suitable for your application. For users who do not use the function block libraries, the program and configuration memory is also available without a license as an option.

## Your advantages

- Program and configuration memory, plug-in, with license key for function block libraries.
- For storing application programs and other files in the file system of the PLC



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 833325
GTIN	4046356833325
Weight per Piece (excluding packing)	8.500 g
Custom tariff number	85235190
Country of origin	Germany

# Program / configuration memory - SD FLASH 512MB APPLIC A - 2701799

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

### General

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	27240400
eCl@ss 4.1	27240400
eCl@ss 5.0	27242200
eCl@ss 5.1	24210100
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

### ETIM

ETIM 3.0	EC000192
ETIM 4.0	EC000192
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	32101601
UNSPSC 13.2	43202005
UNSPSC 18.0	32101606
UNSPSC 19.0	32101606
UNSPSC 20.0	32101606
UNSPSC 21.0	32101606

## Program / configuration memory - SD FLASH 512MB APPLIC A - 2701799

### Accessories

#### Accessories

#### Controller

##### Controller - ILC 131 ETH - 2700973



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

---

##### Controller - ILC 131 ETH/XC - 2701034



Inline controller for use under harsh ambient conditions, with Ethernet interface for coupling to other controllers and systems, with programming options according to IEC 61131-3, complete with connector and labeling field.

---

##### Controller - ILC 151 ETH - 2700974



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

---

##### Controller - ILC 151 ETH/XC - 2701141



Inline controller for use under harsh ambient conditions, with Ethernet interface for coupling to other controllers and systems, with programming options according to IEC 61131-3, complete with connector and labeling field.

---

##### Controller - ILC 171 ETH 2TX - 2700975



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

---

## Program / configuration memory - SD FLASH 512MB APPLIC A - 2701799

### Accessories

Controller - ILC 191 ETH 2TX - 2700976



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

---

Controller - ILC 191 ME/AN - 2700074



Inline controller with integrated pulse/direction/PWM interface, RS-485/RS-422, analog inputs (0 ... 10 V), and analog outputs (0 ... 10 V), with programming options according to IEC 61131-3

---

Controller - ILC 191 ME/INC - 2700075



Inline controller with integrated pulse/direction/PWM interface, RS-485/RS-422, fast counters, and incremental encoder inputs, with programming options according to IEC 61131-3

---

Controller - AXC 1050 - 2700988



Axio control for direct open-loop control of Axioline I/Os. With 2 Ethernet interfaces and programming capabilities according to IEC 61131-3. Complete with connector connector and labeling field.

---

Controller - AXC 1050 XC - 2701295



Axiocontrol for the direct control of Axioline I/Os. With 2 Ethernet interfaces, extended temperature range, and programming options according to IEC 61131-3. Complete with connector connector and marking field.

---