

Product data sheet

Characteristics

LX1D2E7

TeSys D - contactor coil - LX1D2 - 48 V AC 50/60 Hz for 9 to 18 A contactor

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D2
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	48 V AC 50/60 Hz
Average resistance	25 Ohm 68 °F (20 °C)
Inductance of closed circuit	1 H
Product compatibility	LC1D09...D18

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational 0.8...1.1 Uc 50/60 Hz 131 °F (55 °C))
Inrush power in VA	70 VA 50/60 Hz 0.75 68 °F (20 °C))
Hold-in power consumption in VA	8 VA 50/60 Hz 0.3 68 °F (20 °C))

Environment

Net weight	1.54 lb(US) (0.7 kg)
------------	----------------------

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901234944
Returnability	No
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
---------------------------	---

Contractual warranty

Warranty	18 months
----------	-----------