

Base element - UM-BE 16,5-1 - 2958053

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Base element without snap foot, for aligning several base elements without ribs, L = 16.5 mm



The figure shows a combination of versions UM-SE-1, UM 16,5-1 BE, UM-BE 35-1, UM-BEFE 35-1, UM-SE-A 60-R and UM-A/U 73 CM

RoHS

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 017918 086060 |
| GTIN | 4017918086060 |
| Weight per Piece (excluding packing) | 8.000 g |
| Custom tariff number | 85369010 |
| Country of origin | Poland |

Technical data

Product properties

| | |
|---------------------------|------------------------------|
| Brief article description | Base element |
| Type | UM-BE 16,5-1 |
| Order No. | 2958053 |
| Housing type | Press-drawn section housings |
| Type | Plug-in module base element |

Dimensions

| | |
|-------|---------|
| Width | 16.5 mm |
| Depth | 111 mm |

Material specifications

| | |
|------------------|-----------|
| Housing material | Polyamide |
|------------------|-----------|

Base element - UM-BE 16,5-1 - 2958053

Technical data

Material specifications

| | |
|-------------|-------|
| Color (RAL) | green |
|-------------|-------|

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
|---------------------------------|-------------------|

Packaging specifications

| | |
|----------------------------|------|
| Pieces per package | 50 |
| Denomination packing units | Pcs. |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V2 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27182701 |
| eCl@ss 4.0 | 27180400 |
| eCl@ss 4.1 | 27180400 |
| eCl@ss 5.0 | 27180500 |
| eCl@ss 5.1 | 27180500 |
| eCl@ss 6.0 | 27180800 |
| eCl@ss 7.0 | 27182701 |
| eCl@ss 8.0 | 27182701 |
| eCl@ss 9.0 | 27182701 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001031 |
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC001031 |
| ETIM 5.0 | EC002779 |
| ETIM 6.0 | EC002779 |
| ETIM 7.0 | EC002779 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11 | 31261501 |
| UNSPSC 12.01 | 31261501 |
| UNSPSC 13.2 | 31261501 |

Base element - UM-BE 16,5-1 - 2958053

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 18.0 | 31261501 |
| UNSPSC 19.0 | 31261501 |
| UNSPSC 20.0 | 31261501 |
| UNSPSC 21.0 | 31261501 |

Approvals


Approvals

Approvals

UL Recognized / EAC

Ex Approvals

Approval details

| | | | |
|---------------|---|---|---------------|
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 240868 |
|---------------|---|---|---------------|

| | | | |
|-----|---|--|---------|
| EAC |  | | B.01742 |
|-----|---|--|---------|