



⚠ Discontinued

LX1D2N7 has not been replaced. Please contact your customer care center for more information.

## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D2
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	415 V AC 50/60 Hz
Average resistance	1938 Ohm 68 °F (20 °C)
Inductance of closed circuit	74 H
Product compatibility	LC1D09...D18

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational 0.8...1.1 Uc 50/60 Hz 131 °F (55 °C))
Inrush power in VA	70 VA 50/60 Hz 0.75 68 °F (20 °C))
Hold-in power consumption in VA	8 VA 50/60 Hz 0.3 68 °F (20 °C))

## Environment

Net weight	1.54 lb(US) (0.7 kg)
------------	----------------------

## Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901873242
Returnability	No
Country of origin	FR

## Contractual warranty

Warranty	18 months
----------	-----------