

PRODUCT-DETAILS

E4.2 W FP Iu=4000 or V version 4p HR HR

E4.2 W FP Iu=4000 or V version 4p HR HR



General Information

Extended Product Type	E4.2 W FP Iu=4000 or V version 4p HR HR
Product ID	1SDA073916R1
EAN	8015644778491
Catalog Description	E4.2 W FP Iu=4000 or V version 4p HR HR
Long Description	FIXED PART WITHDRAWABLE FOR C.BREAKER SACE EMAX2 E4.2 4000 FOUR-POLE WITH REAR HORIZONTAL TERMINALS (VERS. V)

Ordering

EAN	8015644778491
Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

Dimensions

Product Net Width	551 mm
Product Net Height	425 mm
Product Net Depth / Length	383 mm
Product Net Weight	62 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	570 mm
Package Level 1 Height	610 mm
Package Level 1 Depth / Length	785 mm
Package Level 1 Gross Weight	69 kg
Package Level 1 EAN	8015644778491

Additional Information

Current Type	AC
Neutral Pole Current ([% Iu])	100 %
Number of Poles	4
Product Main Type	SACE Emax 2
Product Name	Fixed Part
Product Type	Fixed Part
Rated Current (I _n)	4000 A
Rated Voltage (U _r)	690 V
Rated Impulse Withstand Voltage (U _{imp})	acc. to IEC 60947-2 12 kV
Rated Insulation Voltage (U _i)	AC 1000 V
Rated Operational Voltage	690 V AC
Rated Uninterrupted Current (I _u)	4000 A
Standards	IEC
Sub-type	E4.2
Terminal Connection Type	Rear flat Horizontal
Version	W FP

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC200023D0204
Declaration of Conformity - CE	1SDL000165R0021
Environmental Information	Not Available
Instructions and Manuals	1SDH001000R0820

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC002043 - Chassis part power circuit breaker
ETIM 7	EC002043 - Chassis part power circuit breaker
Object Classification Code	Q
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Air Circuit Breakers → Emax 2

